

P-FU 6,3X32 LED 24 - Fuse plug

3046508

<https://www.phoenixcontact.com/us/products/3046508>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block., nominal current: 10 A, connection method: Plug-in connection, fuse type: G / 6,3 x 32, mounting type: Plug-in mounting, color: black

Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection

Commercial data

Item number	3046508
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
Catalog page	Page 414 (C-1-2019)
GTIN	4046356113120
Weight per piece (including packing)	6.57 g
Weight per piece (excluding packing)	6.57 g
Customs tariff number	85369095
Country of origin	PL

P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Technical data

Notes

Notes on operation	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
--------------------	---

Product properties

Product type	Fuse
Potentials	1

Data management status

Article revision	03
------------------	----

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Fuse	G / 6,3 x 32
LED voltage range	12 V DC ... 30 V DC
LED current range	0.31 mA ... 0.95 mA

Input data

LED voltage range	12 V DC ... 30 V DC
-------------------	---------------------

Connection data

Nominal current	10 A (the current is determined by the fuse used)
Maximum load current	10 A (the current is determined by the fuse used)

Dimensions

Width	8.2 mm
Height	40 mm
Depth	27 mm
Length	40 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3

P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Plug-in mounting
Thread type	()

P-FU 6,3X32 LED 24 - Fuse plug


3046508

<https://www.phoenixcontact.com/us/products/3046508>



Drawings

Circuit diagram




P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks


P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

P-FU 6,3X32 LED 24 - Fuse plug


3046508


<https://www.phoenixcontact.com/us/products/3046508>





Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3046508>

 CSA Approval ID: 2030668				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	24 V	10 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00714				
---	--	--	--	--

 cULus Recognized Approval ID: E60425				
--	--	--	--	--

 cULus Recognized Approval ID: E60425				
--	--	--	--	--

 cULus Recognized Approval ID: E60425				
--	--	--	--	--

P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Classifications

ECLASS

ECLASS-11.0	27141149
ECLASS-12.0	27141149
ECLASS-13.0	27250305

ETIM

ETIM 9.0	EC002018
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

P-FU 6,3X32 LED 24 - Fuse plug



3046508

<https://www.phoenixcontact.com/us/products/3046508>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com