




Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: Pin

Mating Pin Diameter: 2.36 mm [.093 in]

Wire Size: 642 - 2582 CMA

Features

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
------------------------------------	-----------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Crimp Wire Terminal Type	Pin
Mating Pin Diameter	2.36 mm[.093 in]
Barrel Type	Open
Terminal Plating Material	Pre-Tin
Contact Shape & Form	Round
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	642 - 2582 CMA
Barrel Inside Diameter	1.27 mm[.05 in]
Terminal Material Thickness	.32 mm[.013 in]



Overall Product Length	21.21 mm[.835 in]
------------------------	-------------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 - 85 °C[-40 - 185 °F]

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 62074-1 PIN .125 (3.17 MM) 24-20 AWG 0.42 BR	 TE Part # 41854 PIN 093 (2.36 MM) REC 22-18 AWG TPBR	 TE Part # 61013-2 PIN .109 (2.77 MM) 18-14 AWG TPBR	 TE Part # 62616-1 PIN .109 (2.77MM) 18-14 AWG 016BR
 TE Part # 60440-1 PIN 093 RECEPTACLE 22-18 AWG BR	 TE Part # 62358-1 PIN .080 (2.03 MM) 24-20 AWG TPBR	 TE Part # 60115-1 PIN 125 REC 22-20 AWG BR	 TE Part # 60115-4 PIN 125 RECEPTACLE 22-20 AWG BR
 TE Part # 62505-1 PIN 130 22-18 AWG .0157 X 1.020 BR	 TE Part # 626361-3 WALL PLUG PIN 0.5/1.5MM2 0.38X36.40 NIBR	 TE Part # 63493-1 112 DIA PIN 30-26 012 PTPBR	

Customers Also Bought

 TE Part # 776273-1 14POS,AMPSEAL,SOC HSG ASSY,SLD, COD 1	 TE Part # 1-1879074-7 THS15 12R 5%	 TE Part # 926869-3 UNIV-MNL SOCKET 1	 TE Part # 770642-1 TIMER CONNECTOR TERMINAL 20-14 AWG PTPBR
 TE Part # 0462-201-20141 SOC, SOLID, SIZE 20, 20AWG, NI	 TE Part # 770520-1 AMPSEAL,TERMINAL,TIN PLATE,16-20AWG WIRE	 TE Part # 926899-3 UNIV-MNL SPLIT ST	 TE Part # 1546670-6 6P .437" DR BARRIER,W/BND SCRW



Documents

Product Drawings

PIN 093 CRIMP TAB 22-16 AWG PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62820-1_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62820-1_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62820-1_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.