



120×120×38 mm

San Ace 120W 9WP type   

General Specifications

- Material Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-1)
- Expected life See the table below. (L10 life: 90% survival rate for continuous operation in indoor free air at 60°C, rated voltage)
- Motor protection function Locked rotor burnout protection, Reverse polarity protection
For details, please refer to p. 547.
- Dielectric strength 50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
- Insulation resistance 10 MΩ or more with a 500 VDC megger (between lead wire conductors and frame)
- Sound pressure level (SPL) At 1 m away from the air inlet
- Storage temperature -30 to +70°C (Non-condensing)
- Lead wire ⊕Red ⊖Black (Sensor) Yellow
- Mass 360 g
- Ingress protection IP68

Specifications

The models listed below **have ribs and pulse sensors**. For models without ribs, append "1" to the end of model numbers.

Model no.	Rated voltage [V]	Operating voltage range [V]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. airflow [m³/min] [CFM]		Max. static pressure [Pa] [inchH ₂ O]		SPL [dB (A)]	Operating temperature [°C]	Expected life [h]		
9WP1212H101	12	7 to 13.8	0.38	4.56	2600	2.8	99	70.4	0.283	39	-20 to +70	40000/60°C		
9WP1212M101			0.21	2.52	1950	2.1	74.2	39.6	0.159	32				
9WP1212L101		10.2 to 13.8	0.14	1.68	1500	1.62	57.2	23.4	0.094	26				
9WP1224H101	24	14 to 27.6	0.22	5.28	2600	2.8	99	70.4	0.283	39				
9WP1224M101			0.11	2.64	1950	2.1	74.2	39.6	0.159	32				
9WP1248H101	48	40.8 to 55.2	0.11	5.28	2600	2.8	99	70.4	0.283	39				
9WP1248M101			0.07	3.36	1950	2.1	74.2	39.6	0.159	32				

The following sensor and control options are available for selection.


Differs according to the model. Refer to the table on pp. 580 to 581.

Without sensor **Lock sensor**

Airflow - Static Pressure Characteristics


9WP1212H101 With pulse sensor

Operating voltage range




9WP1212M101 With pulse sensor

Operating voltage range



9WP1212L101 With pulse sensor


Operating voltage range



Airflow - Static Pressure Characteristics


9WP1224H101 With pulse sensor

Operating voltage range




9WP1224M101 With pulse sensor

Operating voltage range




9WP1248H101 With pulse sensor

Operating voltage range





9WP1248M101 With pulse sensor


Operating voltage range



Dimensions (unit: mm) (With ribs)



■ **Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**



■ **Options**

Finger guards	page: p. 533	Resin finger guards	page: p. 539
Model no.: 109-019E, 109-019K, 109-019C, 109-019H		Model no.: 109-1000G	