

San Ace 60

9GA type

Low Power Consumption Fan

Features

Low Power Consumption

Achieves a low power consumption of 3.24 W.*

High Static Pressure and High Airflow

Achieves a maximum static pressure of 66 Pa, and a maximum airflow of 0.62 m³/min.*

* : Specification of Model No. 9GA0612G9001.



60×60×10_{mm}

Specifications

The following nos. have **pulse sensors**.

Model No.	Rated voltage [V]	Operating voltage range [V]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. Aiflow [m ³ /min] [CFM]	Max. Static pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9GA0612G9001	12	7 to 13.2	0.27	3.24	6,200	0.62 21.9	66 0.26	43	-20 to +60	40,000 / 60 °C (70,000 / 40 °C)
9GA0612H9001		7 to 13.8	0.14	1.68	5,000	0.50 17.6	42.9 0.17	37	-20 to +70	
9GA0612L9001			0.03	0.36	2,300	0.23 8.1	9.1 0.037	17	-10 to +70	




Available options: **Without sensor** **Lock sensor**

Common Specifications

- ☐ Material Frame, Impeller: Plastics (Flammability: UL94V-0)
- ☐ Expected life Refer to specifications
(L10: Survival rate: 90% at 60 °C, rated voltage, and continuously run in a free air state)
- ☐ Motor protection system Current blocking function and reverse polarity protection
- ☐ Dielectric strength 50 / 60 Hz, 500 VAC, 1 minute (between lead conductor and frame)
- ☐ Sound pressure level (SPL) Expressed as the value at 1 m from air inlet side
- ☐ Operating temperature Refer to specifications (Non-condensing)
- ☐ Storage temperature -30 °C to +70 °C (Non-condensing)
- ☐ Lead wire ⊕Red ⊖Black Sensor: Yellow
- ☐ Mass Approx. 35 g


Airflow - Static Pressure Characteristics

- Operating voltage range




Specifications for Pulse Sensors


Output circuit: Open collector



Output waveform (Need pull-up resistor)



Dimensions (unit: mm)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)

