

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output DC-DC Converter



3.3Vin

- ⊕ Continuous short-circuit protection
- ⊕ High efficiency up to 80%
- ⊕ No-load input current as low as 8mA
- ⊕ I/O isolation test voltage 1.5kVDC
- ⊕ Operating ambient temp. range: -40°C to +105°C
- ⊕ Industry standard pin-out



DC-DC Converter

1 Watt

The 1S4AE_1.5UP series is especially designed for distributed power supply systems where an isolated voltage is required. They are suitable for occasions of: pre-interference isolation, ground interference elimination, pure digital circuit, voltage isolation conversion, general low frequency analog circuit, relay drive circuit, etc.

Common specifications

Short Circuit Protection	Continuous, self-recovery		
Operating Temperature	-40 ~ 105°C; Derating if the temperature ≥ 85°C, (see Fig. 2)		
Storage Temperature	-55 ~ 125°C		
Casing Temperature Rise	Ta=25°C; 25 °C		
Pin Welding Resistance Temperature	Welding spot is 1.5mm away from the casing, 10 seconds	300°C	
Storage Humidity	Non-condensing	95 %RH	
Switching Frequency	100% load, nominal input voltage	20KHz	
MTBF	3500,000h (MIL-HDBK-217F@25 °C)		
Casing Material	Black flame-retardant and heat-resistant plastic (UL94 V-0)		
Package Dimensions	11.60x6.00x10.16mm		
Weight	1.3g (Typ.)		
Cooling methods	Free air convection		

Output specifications

Item	Test condition	Min	Typ	Max	Units
Output voltage accuracy	See output regulation curve (Fig. I)				
Line regulation	Input voltage change: ±1% • 3.3VDC output • Others				
		1.5	1.2	%	%
Load regulation	10% to 100% load • 3.3VDC output • Others	30	75	100	%
		50	100	100	%
Ripple & Noise*	20MHz Bandwidth • 3.3/5/9/l2/5VDC output • 24VDC output	30	75	100	mVp-p
		50	100	100	mVp-p
Temperature Drift Coefficient	100% load	±0.02		%/°C	

Note: • The 'parallel cable' method is used for Ripple and Noise test, please refer to DC-DC Converter Application Notes for specific information.

EMC specifications

Emissions	CE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
Emissions	RE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
Immunity	ESD	IEC/EN61000-4-2	Contact ±6kV perf. Criteria B

Example:

1S4AE_0305S1.5UP

1 = 1Watt; S4 = SIP4; A = Pinning; E = Cost effective; 3 = 3.3Vin; 05 = 5Vout; S = Single Output; 1.5 = 1.5kVDC; U = Unregulated output; P = Short circuit protection

Note:

- If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- The maximum capacitive load offered were tested at input voltage range and full load;
- Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta = 25°C, humidity <75%RH with nominal input voltage and rated output load;
- All index testing methods in this datasheet are based on our Company's corporate standards;
- We can provide product customization service, please contact our technicians directly for specific information;
- Products are related to laws and regulations: see "Features" and "EMC";
- Classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Input specifications

Item	Test condition	Min	Typ	Max	Units
Input current (full load / no-load)	• 3.3/5VDC output • Others output	405/8 379/8	427/- 399/-	mA	mA
Reflected ripple current*		30		mA	
Surge Voltage (1sec. max.)		-0.7	5	VDC	
Input filter	Capacitor filter				
Hot plug	Unavailable				

* Refer to DC-DC Converter Application Notes for detailed description of reflected ripple current test method.

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Product Selection Guide

Part Number	Certification	Input Voltage [VDC] Nominal	Input Voltage [VDC] Range	Output Voltage [VDC]	Output Current [mA, Max./Min]	Efficiency ⁽²⁾ [%], Min./Typ.] @ Full Load	Capacitive load [μ F, Max]
1S4AE_0303S1.5UP		3.3	2.97-3.63	3.3	303/30	71/75	2400
1S4AE_0305S1.5UP		3.3	2.97-3.63	5	200/20	76/80	2400
1S4AE_0312S1.5UP		3.3	2.97-3.63	9	111/12	76/80	1000
1S4AE_0312S1.5UP		3.3	2.97-3.63	12	83/8	76/80	560
1S4AE_0315S1.5UP		3.3	2.97-3.63	15	67/7	76/80	560
1S4AE_0324S1.5UP		3.3	2.97-3.63	24	42/4	76/80	220

Typical Characteristic Curves




Fig.1





Fig. 2

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Typical application

If it is required to further reduce input and output ripple, a filter capacitor can be connected to the input and output terminals, see Fig.3. Moreover, choosing suitable filter capacitor is very important, start-up problems may be caused by too large capacitance. To ensure the modules running well, the recommended capacitive load values as shown in Table 1.



Recommended capacitive load value table (Table 1)

Vin (VDC)	Cin(µF)	Vout (VDC)	Cout (µF)
3.3	2.2µF/25V	3.3VDC/5VDC	10µF/16V
		9VDC	2.2µF/16V
		12VDC	2.2µF/25V
		15VDC	1µF/25V
		24VDC	1µF/50V

EMC solution-recommended circuit





Table 2: Recommended EMC filter values

Emissions	C1/C2	4.7µF /50V
	C3	Refer to the Cout in Rg.3
	LDM	6.8µH
	CY	270pF /2kV

Mechanical dimensions and recommended layout



1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output DC-DC Converter



5Vin

- Continuous short-circuit protection
- No-load input current as low as 5mA
- Operating temperature range: -40°C to +105°C
- High efficiency up to 85%
- Isolation voltage: 1.5kVDC/min, 3kVDC/1s
- International standard pin-out
- Compact SIP package
- Meets UL62368, EN62368



DC-DC Converter

1 Watt

The 1S4AE_1.5UP series are specially designed for applications where an isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits.

Common specifications

Short Circuit Protection		Continuous, self-recovery			
Operating Temperature		-40 ~ 105°C Derating if the temperature $\geq 85^\circ\text{C}$, (see Fig. 2)			
Storage Temperature		-55 ~ 125°C			
Casing Temperature Rise	Ta=25°C • 3.3VDC output • Other output	25 15	°C °C		
Pin Welding Resistance Temperature	Welding spot is 1.5mm away from the casing, 10 seconds			300°C	
Storage Humidity	Non-condensing			95 %RH	
Switching Frequency	100% load, nominal input voltage	270	KHz		
MTBF	3500,000h (MIL-HDBK-217F@25)				
Casing Material	Black flame-retardant and heat-resistant plastic (UL94 V-0)				
Package Dimensions	11.60x6.00x10.16mm				
Weight	1.3g (Typ.)				
Cooling methods	Free air convection				

Output specifications

Item	Test condition	Min	Typ	Max	Units
Output voltage accuracy		See tolerance envelope curve(Fig. 1)			
Line regulation		Input voltage change: $\pm 1\%$ • 3.3VDC output • Others			
				1.5	%
				1.2	%
Load regulation		10% to 100% load • 3.3VDC output • 5VDC output • 9VDC output • 12VDC output • 15VDC output • 24VDC output			
			15	20	%
			10	15	%
			8	10	%
			7	10	%
			6	10	%
			5	10	%
Ripple & Noise*		20MHz Bandwidth • Other output • 24VDC output			
			30	75	mVp-p
			50	100	mVp-p
Temperature Drift Coefficient		100% load			
			± 0.02		
			%/°C		

Note: *Ripple and noise tested with "parallel cable" method, please see DC-DC Converter Application Notes for specific operation methods.

Isolation specifications

Item	Test condition	Min	Typ	Max	Units
Isolation voltage	Input-output, leak current lower than 1mA • 1 minute test time • 1 second test time	1500 3000			VDC
Isolation resistance	IO, test at 500VDC	1000			MΩ
Isolation capacitance	IO , 100KHz/0.1V	20			pF

EMC specifications

Emissions	CE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
Emissions	RE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
Immunity	ESD	IEC/EN61000-4-2	Air $\pm 8\text{kV}$, Contact $\pm 4\text{kV}$ perf. Criteria B

Example:

1S4AE_0505S1.5UP

1 = 1Watt; S4 = SIP4; A = Pinning; E = Cost effective; 05 = 5Vin; 05 = 5Vout; S = Single Output; 1.5 = 1.5kVDC; U = Unregulated output; P = Short circuit protection

Input specifications

Item	Test condition	Min	Typ	Max	Units
Input current (full load / no-load)	• 3.3/5VDC output • 9/12VDC output • 15/24VDC output	270/5 241/12 241/18	286/10 254/20 254/30	mA	mA
Reflected ripple current*		15			mA
Surge Voltage (1sec. max.)		-0.7	9		VDC
Input filter	Capacitor filter				
Hot plug	Unavailable				

* Reflected ripple current testing method please see DC-DC Converter Application Notes for specific operation.

Note:

- If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- The maximum capacitive load offered were tested at input voltage range and full load;
- Unless otherwise specified, parameters in this datasheet were measured under the conditions of $T_a = 25^\circ\text{C}$, humidity $<75\%$ RH with nominal input voltage and rated output load;
- All index testing methods in this datasheet are based on our Company's corporate standards;
- We can provide product customization service, please contact our technicians directly for specific information;
- Products are related to laws and regulations: see "Features" and "EMC";
- Classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Product Selection Guide

Part Number	Certification	Input Voltage [VDC] Nominal	Input Voltage [VDC] Range	Output Voltage [VDC]	Output Current [mA, Max./Min]	Efficiency ⁽²⁾ [%], Min./Typ.] @ Full Load	Capacitive load [μ F, Max]
1S4AE_0503S1.5UP		5	4.5-5.5	3.3	303/30	70/74	2400
1S4AE_0505S1.5UP		5	4.5-5.5	5	200/20	78/82	2400
1S4AE_0512S1.5UP		5	4.5-5.5	9	111/12	79/83	1000
1S4AE_0512S1.5UP		5	4.5-5.5	12	84/9	79/83	560
1S4AE_0515S1.5UP		5	4.5-5.5	15	67/7	79/83	560
1S4AE_0524S1.5UP		5	4.5-5.5	24	42/4	81/85	220

Typical Characteristic Curves










Fig. 2



1S4AE_1.5UP series


1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Efficiency curves



Typical application


If it is required to further reduce input and output ripple, a filter capacitor can be connected to the input and output terminals, see Fig.3. Moreover, choosing suitable filter capacitor is very important, start-up problems may be caused by too large capacitance. To ensure the modules running well, the recommended capacitive load values as shown in Table 1.



Recommended capacitive load value table (Table 1)

Vin (VDC)	Cin(μF)	Vout (VDC)	Cout (μF)
5	4.7	3.3/5	10
		9/12	2.2
		15/24	1

EMC solution-recommended circuit



EMC recommended circuit value table (Table 2)

Input voltage 5VDC	Output voltage (VDC)	3.3/5/9	12/15/24
		C1/C2	4.7μF /25V
EMI	CY		1nF/4KVDC VISHAY HGZ102MBP TDK CD45-E2GA102M-GK
	C3		Refer to the Cout in table 1
	LDM	6.8μH	6.8μH



Note:

In the case of actual use, the requirements for EMI are high, it is subject to CY.

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Mechanical dimensions and recommended layout




Note:

Unit :mm[inch]

Pin section tolerances :±0.10[±0.004]

General tolerances:±0.25[±0.010]

THIRD ANGLE PROJECTION



Note : Grid 2.54*2.54mm

Pin-Out	
Pin	Function
1	GND
2	Vin
3	0V
4	+Vo

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output DC-DC Converter



12/15/24Vin

- Continuous short-circuit protection
- No-load input current as low as 8mA
- Operating temperature range: -40°C to +105°C

- High efficiency up to 81%
- I/O isolation test voltage: 1.5kVDC
- Industry standard pin-out
- IEC62368, UL62368, EN62368 approved



UL-62368-1 (E347551)

DC-DC Converter

1 Watt

The 1S4AE_1.5UP series are specially designed for applications where an isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits

Output specifications

Item	Test condition	Min	Typ	Max	Units
Short Circuit Protection	Continuous, self-recovery				
Operating Temperature	Derating if the temperature $\geq 85^{\circ}\text{C}$, (see Fig. 2)	-40	105	$^{\circ}\text{C}$	
Storage Temperature		-55	125	$^{\circ}\text{C}$	
Casing Temperature Rise	Ta=25°C, nominal input, full load output	25		$^{\circ}\text{C}$	
Pin Welding Resistance Temperature	Welding spot is 1.5mm away from the casing, 10s	300		$^{\circ}\text{C}$	
Storage Humidity	Non-condensing	5	95	%RH	
Vibration	10-150Hz, 5G, 0.75mm. along X, Y and Z				
Switching Frequency	Full load, nominal input voltage	260		KHz	
MTBF	MIL-HDBK-217F@25	3500,000		h	
Casing Material	Black plastic; flame-retardant and heat-resistant (UL94 V-0)				
Package Dimensions	11.60*6.00*10.16mm				
Weight	1.3g (Typ.)				
Cooling methods	Free air convection				

Output specifications

Item	Test condition	Min	Typ	Max	Units
voltage accuracy	See output regulation curves (Fig. 1)				
Line regulation	Input voltage change: $\pm 1\%$ • 3.3VDC output • 5VDC output • 9VDC output • 12VDC output • 15VDC output • 24VDC output			1.5	%
				1.2	%
Load regulation	10% to 100% load • 3.3VDC output • 5VDC output • 9VDC output • 12VDC output • 15VDC output • 24VDC output		8	20	%
			5	15	%
			3	10	%
			3	10	%
			3	10	%
			2	10	%
Ripple & Noise*	20MHz Bandwidth • 3.3/5/9/12/15VDC output • 24VDC output	30	75	mVp-p	
		50	100	mVp-p	
Temperature Drift Coefficient	Full load			± 0.02	%/ $^{\circ}\text{C}$

* The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.

Example:

1S4AE_1203S1.5UP

1 = 1Watt; S4 = SIP4; A = Pinning; E = Cost effective; 12 = 12Vin; 03 = 3Vout; S = Single Output; 1.5 = 1.5kVDC; U = Unregulated

Input specifications

Item	Test condition	Min	Typ	Max	Units
Input current (full load / no-load)	12V input • 3.3VDC output • 5/9/12VDC output • 15/24VDC output 15V input • 5/9/12VDC output • 15/24VDC output 24V input • 3.3VDC output • 5VDC output • 9VDC output • 12/15/24VDC output	112/8	118	mA	
		105/8	110	mA	
		103/8	109	mA	
		84/8	88	mA	
		83/8	87	mA	
		56/8	61	mA	
		53/8	58	mA	
		53/8	57	mA	
		52/8	56	mA	
Reflected ripple current		15		mA	
Surge Voltage (1sec. max.)	• 12VDC input • 15VDC input • 24VDC input	-0.7	18	VDC	
		-0.7	21	VDC	
		-0.7	30	VDC	
Input filter	Capacitor filter				
Hot plug	Unavailable				

* Reflected ripple current testing method please see DC-DC Converter Application Notes for specific operation.

Isolation specifications

Item	Test condition	Min	Typ	Max	Units
Isolation voltage	I/O, test for 1 minute, leak current of 1mA	1500			VDC
Isolation resistance	IO, test at 500VDC	1000			MΩ
Isolation capacitance	IO, 100KHz/0.1V		20		pF

EMC specifications

EMI	CE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
EMI	RE	CISPR32/EN55032	CLASS B (EMC recommended circuit)
EMS	ESD	IEC/EN61000-4-2	Air $\pm 8\text{kV}$, Contact $\pm 4\text{kV}$ perf. Criteria B

Note:

- If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- The maximum capacitive load offered were tested at input voltage range and full load;
- Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta = 25°C, humidity <75%RH with nominal input voltage and rated output load;
- All index testing methods in this datasheet are based on our Company's corporate standards;
- We can provide product customization service, please contact our technicians directly for specific information;
- Products are related to laws and regulations: see "Features" and "EMC";
- Classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Product Selection Guide

Part Number	Certification	Input Voltage [VDC] Nominal Range	Output Voltage [VDC]	Output Current [mA, Max./Min]	Full Load Efficiency [% Min./Typ.]	Capacitive load [μ F, Max]
1S4AE_1203S1.5UP	UL	12	(10.8-13.2)	3.3	303/30	71/75
1S4AE_1205S1.5UP	UL	12	(10.8-13.2)	5	200/20	76/80
1S4AE_1209S1.5UP	UL	12	(10.8-13.2)	9	111/12	76/80
1S4AE_1212S1.5UP	UL	12	(10.8-13.2)	12	83/9	76/80
1S4AE_1215S1.5UP	UL	12	(10.8-13.2)	15	67/7	77/81
1S4AE_1224S1.5UP	UL	12	(10.8-13.2)	24	42/5	77/81
1S4AE_1505S1.5UP	UL	15	(13.5-16.5)	5	200/20	76/80
1S4AE_1509S1.5UP	UL	15	(13.5-16.5)	9	111/12	76/80
1S4AE_1512S1.5UP	UL	15	(13.5-16.5)	12	83/9	76/80
1S4AE_1515S1.5UP	UL	15	(13.5-16.5)	15	67/7	77/81
1S4AE_1524S1.5UP	-	15	(13.5-16.5)	24	42/5	77/81
1S4AE_2403S1.5UP	UL	24	(21.6-26.4)	3.3	303/30	71/75
1S4AE_2405S1.5UP	UL	24	(21.6-26.4)	5	200/20	76/80
1S4AE_2409S1.5UP	UL	24	(21.6-26.4)	9	111/12	76/80
1S4AE_2412S1.5UP	UL	24	(21.6-26.4)	12	83/9	76/80
1S4AE_2415S1.5UP	UL	24	(21.6-26.4)	15	67/7	77/81
1S4AE_2424S1.5UP	UL	24	(21.6-26.4)	24	42/5	77/81

Typical Characteristic Curves




Fig. 1








Fig. 2

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Efficiency curves



Typical application

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig.3. Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1.




Table 1: Recommended input and output capacitor values

V_{in} (VDC)	C_{in} (μ F)	V_{out} (VDC)	C_{out} (μ F)
12VDC	2.2 μ F/25V	3.3VDC	10 μ F/16V
15VDC	2.2 μ F/25V	5VDC	10 μ F/16V
24VDC	1 μ F/50V	9VDC	2.2 μ F/16V
		12VDC	2.2 μ F/25V
		15VDC	1 μ F/25V
		24VDC	1 μ F/50V

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

EMC solution-recommended circuit





Fig. 4

Emissions	C1	4.7 μ F /50V
	C2	4.7 μ F /50V
	C3	Refer to the Cout in Fig.3
	LDM	6.8 μ H
	CY	270pF/2kV

Mechanical dimensions and recommended layout



Note:

Unit :mm[inch]

Pin section tolerances : ± 0.10 [± 0.004]

General tolerances: ± 0.25 [± 0.010]