


DO NOT
SCALE FROM
THIS PRINT

No. OF POSITIONS PER ROW

- 01: 1 POSITION (SEE NOTE 4)
- 02: 2 POSITIONS
- 04: 4 POSITIONS
- 06: 6 POSITIONS
- 08: 8 POSITIONS
- *-10: 10 POSITIONS


(*=NOT TOOLED)

LEAD STYLE

- *-02.0 (SEE TABLE 1 & 5)
- *-03.0 (SEE TABLE 1 & 6)
- *-04.0 (SEE TABLE 1 & 6)
- *-05.0 (SEE TABLE 1 & 6)
- *-06.0 (SEE TABLE 1 & 6)
- *-07.0 (SEE TABLE 1 & 6)
- *-08.0 (SEE TABLE 1 & 6)
- *-09.0 (SEE TABLE 1 & 6)
- *-10.0 (SEE TABLE 1 & 6)
- *-11.0 (SEE TABLE 1 & 6)

(* NOT TOOLED)

IP5-XX-XX.X-X-X-X-X-TR

PACKAGING
-TR: TAPE & REEL
(SEE NOTE 3)OPTION
-L: CABLE LATCH
(SEE NOTE 5)TAIL OPTIONS
-1: .062" THICK BOARD
-2: .093" THICK BOARD
(*= NOT TOOLED)ROW
-S: SINGLE ROW
-D: DOUBLE ROW
(SEE NOTE 4)PLATING OPTIONS
-S: SELECTIVE, 30 Au / 50 Ni MIN ON
CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL

(*=NOT TOOLED)


FIG.1
(IP5-04-05.0-L-S-X SHOWN)

TABLE 1

IP5 LEAD STYLE	IP-XX-XX.X-X P/N	ITP 5-XX.X-X-X P/N
*IP5-XX-02.0-X-XX-X	*IP-XX-02.0-X	*ITP5-02.0-X-XX
*IP5-XX-03.0-X-XX-X	*IP-XX-03.0-X	*ITP5-03.0-X-XX
*IP5-XX-04.0-X-XX-X	*IP-XX-04.0-X	*ITP5-04.0-X-XX
IP5-XX-05.0-X-XX-X	IP-XX-05.0-X	ITP5-05.0-X-XX
*IP5-XX-06.0-X-XX-X	*IP-XX-06.0-X	*ITP5-06.0-X-XX
*IP5-XX-07.0-X-XX-X	*IP-XX-07.0-X	*ITP5-07.0-X-XX
*IP5-XX-08.0-X-XX-X	*IP-XX-08.0-X	*ITP5-08.0-X-XX
*IP5-XX-09.0-X-XX-X	*IP-XX-09.0-X	*ITP5-09.0-X-XX
*IP5-XX-10.0-X-XX-X	*IP-XX-10.0-X	*ITP5-10.0-X-XX
*IP5-XX-11.0-X-XX-X	*IP-XX-11.0-X	*ITP5-11.0-X-XX

(*= NOT TOOLED)

TABLE 2

LEAD STYLE	"A" (REF)	"G" (REF)
*-02.0	0.2400 [6.096]	0.0340 [0.864]
*-03.0	0.2794 [7.096]	0.0734 [1.864]
*-04.0	0.3187 [8.096]	0.1127 [2.864]
-05.0	0.3581 [9.096]	0.1521 [3.864]
*-06.0	0.3975 [10.096]	0.1915 [4.864]
*-07.0	0.4369 [11.096]	0.2309 [5.864]
*-08.0	0.4762 [12.096]	0.2702 [6.864]
*-09.0	0.5156 [13.096]	0.3096 [7.864]
*-10.0	0.5550 [14.096]	0.3490 [8.864]
*-11.0	0.5943 [15.096]	0.3883 [9.864]

(*= NOT TOOLED)

TABLE 3

No. POS PER ROW	"B" (REF)	"C" (REF)	"D"	"E" +/- .0050
-01	0.328 [8.32]	0.228 [5.78]	N/A	N/A
-02	0.485 [12.32]	0.385 [9.78]	1	0.1575 [4.001]
-04	0.800 [20.32]	0.700 [17.78]	3	0.4725 [12.002]
-06	1.115 [28.32]	1.015 [25.78]	5	0.7875 [20.003]
-08	1.430 [36.32]	1.330 [33.78]	7	1.1025 [28.004]
*-10	1.745 [44.32]	1.645 [41.78]	9	1.4175 [36.005]

(*= NOT TOOLED)

NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM PUSH OUT FORCE .5 LBS. [0.23 Kg.]
3. FOR QUANTITIES UP TO 49 PCS., NO LEADER, TRAILER OR REEL WILL BE SUPPLIED,
FOR QUANTITIES OF 50 TO 124 PCS., NO LEADER OR TRAILER WILL BE SUPPLIED.
4. -01 POSITION NOT AVAILABLE WITH -D ROW OPTION
5. -L: CABLE LATCH OPTION ONLY AVAILABLE IN -05.0 LEAD STYLE & -S ROW OPTION.
6. LOAD WELD TAB WITH LANCES FACING INWARD.

-TAIL OPTION	"F"
-1	0.060 [1.52]
*-2	0.090 [2.29]

(*= NOT TOOLED)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (MILLIMETERS)

TOLERANCES ARE:

DECIMALS

ANGLES

.XX: ±.01 [3]

.XXX: ±.005 [13]

.XXXX: ±.0030 [706]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
BODY: HIGH TEMP NYLON, COLOR: BLACK
SHIELD: COPPER ALLOY
TERMINAL: COPPER ALLOY
DIELECTRIC: LCP, COLOR: BLACK

SHEET SCALE: 4:1

DESCRIPTION: TERMINAL ARRAY ASSEMBLY, IP5 CONNECTOR

DWG. NO.


IP5-XX-XX.X-X-X-X-X-X-TR

BY: PIERCE 11/10/2007 SHEET 1 OF 3


520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

F:\DWG\MISC\Mktg\IP5-XX.X-X-X-X-X-TR-MKT.SLDDRW

REVISION C



SECTION "A"-A"
SCALE 5 : 1



SECTION "B"-B"
SCALE 10 : 1




FIG.3
(IP5-04-02.0-L-S-X SHOWN)
(SAME AS FIG. 1, EXCEPT AS SHOWN)







FIG.2
(IP5-04-XX.X-L-D-X SHOWN)
(SAME AS FIG. 1, EXCEPT AS SHOWN)



SECTION "C"-C"
SCALE 3 : 1



SECTION "F"-F"
SCALE 3 : 1



SECTION "G"-G"
SCALE 5 : 1

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 4:1




TABLE 7		
POS	"H" (REF)	"J"
*-01	0.638 [16.19]	0.515 [13.07]
-02	0.795 [20.19]	0.672 [17.07]
-04	1.110 [28.19]	0.987 [25.07]
-06	1.425 [36.20]	1.302 [33.08]
-08	1.740 [44.20]	1.617 [41.08]
*-10	2.055 [52.20]	1.932 [49.08]

(*= NOT TOOLED)





FIG.4
(IP5-04-05.0-L-S-X-L SHOWN)
(SAME AS FIG. 1, EXCEPT AS SHOWN)



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 4:1

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
TERMINAL ARRAY ASSEMBLY, IP5 CONNECTOR

DWG. NO.
IP5-XX-XX.X-X-X-X-X-TR

BY: PIERCE 11/10/2007 SHEET 3 OF 3