



# SiC Power MOSFET

$$\begin{aligned}
 I_{D25} &= 38 \text{ A} \\
 V_{DSS} &= 1200 \text{ V} \\
 R_{DS(on) \text{ max}} &= 52 \text{ m}\Omega
 \end{aligned}$$

**Part number**  
 MCB30P1200LB



 E72873



## Features / Advantages:

- High speed switching with low capacitances
- High blocking voltage with low  $R_{DS(on)}$
- Easy to parallel and simple to drive
- Resistant to latch-up
- Real Kelvin source connection

## Applications:

- Solar inverters
- High voltage DC/DC converters
- Motor drives
- Switch mode power supplies
- UPS
- Battery chargers
- Induction heating

## Package: SMPD

- DCB isolated backside
- Isolation Voltage 2500 V
- Epoxy meets UL 94V-0
- RoHS compliant
- Advanced power cycling

## Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).




| MOSFET        |                                         |                                                                                                                                                                                  |      | Ratings |      |     |  |
|---------------|-----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|---------|------|-----|--|
| Symbol        | Definitions                             | Conditions                                                                                                                                                                       | min. | typ.    | max. |     |  |
| $V_{(BR)DSS}$ | drain source breakdown voltage          | $I_D = 100 \mu A$                                                                                                                                                                | 1200 |         |      | V   |  |
| $V_{GS(max)}$ | max transient gate source voltage       |                                                                                                                                                                                  | -10  |         | +25  | V   |  |
| $V_{GS}$      | continous gate source voltage           | recommended operational value                                                                                                                                                    | -5   |         | +20  | V   |  |
| $I_{D25}$     | drain current                           | $V_{GS} = 20 V$                                                                                                                                                                  |      |         | 38   | A   |  |
| $I_{D80}$     |                                         |                                                                                                                                                                                  |      |         | 30   | A   |  |
| $I_{D100}$    |                                         |                                                                                                                                                                                  |      |         | 27   | A   |  |
| $R_{DS(on)}$  | static drain source on resistance       | $I_D = 40 A; V_{GS} = 20 V$                                                                                                                                                      |      | 40      | 52   | mΩ  |  |
|               |                                         |                                                                                                                                                                                  |      | 90      |      | mΩ  |  |
| $V_{GS(th)}$  | gate threshold voltage                  | $I_D = 10 mA; V_{GS} = V_{DS}$                                                                                                                                                   | 2.0  | 2.6     | 4.0  | V   |  |
|               |                                         |                                                                                                                                                                                  |      | 2.0     |      | V   |  |
| $I_{DSS}$     | drain source leakage current            | $V_{DS} = 1200 V; V_{GS} = 0 V$                                                                                                                                                  |      | 1       | 100  | μA  |  |
| $I_{GSS}$     | gate source leakage current             | $V_{DS} = 0 V; V_{GS} = 20 V$                                                                                                                                                    |      |         | 250  | nA  |  |
| $R_G$         | internal gate resistance                | $f = 1 MHz; V_{AC} = 25 mV$ , ESR of $C_{ISS}$                                                                                                                                   |      | 1.8     |      | Ω   |  |
| $C_{iss}$     | input capacitance                       | $V_{DS} = 1000 V; V_{GS} = 0 V; f = 1 MHz$                                                                                                                                       |      | 1895    |      | pF  |  |
| $C_{oss}$     | output capacitance                      |                                                                                                                                                                                  |      | 150     |      | pF  |  |
| $C_{rss}$     | reverse transfer (Miller) capacitance   |                                                                                                                                                                                  |      | 10      |      | pF  |  |
| $Q_g$         | total gate charge                       | $V_{DS} = 800 V; I_D = 40 A; V_{GS} = -5/20 V$                                                                                                                                   |      | 115     |      | nC  |  |
| $Q_{gs}$      | gate source charge                      |                                                                                                                                                                                  |      | 28      |      | nC  |  |
| $Q_{gd}$      | gate drain (Miller) charge              |                                                                                                                                                                                  |      | 37      |      | nC  |  |
| $t_{d(on)}$   | turn-on delay time                      | Inductive switching $T_{VJ} = 25^\circ C$<br>Free Wheeling Diode: Body Diode @ $V_{GS} = -5V$<br>$V_{DS} = 800 V; I_D = 40 A$<br>$V_{GS} = -5/20 V; R_G = 15 \Omega$ (external)  |      | 25.5    |      | ns  |  |
| $t_r$         | current rise time                       |                                                                                                                                                                                  |      | 11.1    |      | ns  |  |
| $t_{d(off)}$  | turn-off delay time                     |                                                                                                                                                                                  |      | 85      |      | ns  |  |
| $t_f$         | current fall time                       |                                                                                                                                                                                  |      | 23      |      | ns  |  |
| $E_{on}$      | turn-on energy per pulse                |                                                                                                                                                                                  |      | 0.92    |      | mJ  |  |
| $E_{off}$     | turn-off energy per pulse               |                                                                                                                                                                                  |      | 0.48    |      | mJ  |  |
| $t_{d(on)}$   | turn-on delay time                      | Inductive switching $T_{VJ} = 150^\circ C$<br>Free Wheeling Diode: Body Diode @ $V_{GS} = -5V$<br>$V_{DS} = 800 V; I_D = 40 A$<br>$V_{GS} = -5/20 V; R_G = 15 \Omega$ (external) |      | 23.5    |      | ns  |  |
| $t_r$         | current rise time                       |                                                                                                                                                                                  |      | 9.8     |      | ns  |  |
| $t_{d(off)}$  | turn-off delay time                     |                                                                                                                                                                                  |      | 93      |      | ns  |  |
| $t_f$         | current fall time                       |                                                                                                                                                                                  |      | 25      |      | ns  |  |
| $E_{on}$      | turn-on energy per pulse                |                                                                                                                                                                                  |      | 1.0     |      | mJ  |  |
| $E_{off}$     | turn-off energy per pulse               |                                                                                                                                                                                  |      | 0.4     |      | mJ  |  |
| $R_{thJC}$    | thermal resistance junction to case     | with heatsink compound; IXYS test setup                                                                                                                                          |      |         | 0.9  | K/W |  |
| $R_{thJH}$    | thermal resistance junction to heatsink |                                                                                                                                                                                  |      | 1.15    |      | K/W |  |

| Source-Drain Diode |                                           |                                                                       |      | Ratings |      |    |  |
|--------------------|-------------------------------------------|-----------------------------------------------------------------------|------|---------|------|----|--|
| Symbol             | Definitions                               | Conditions                                                            | min. | typ.    | max. |    |  |
| $V_{SD}$           | forward voltage drop                      | $I_F = 20 A; V_{GS} = -5 V$                                           |      | 4.1     |      | V  |  |
|                    |                                           |                                                                       |      | 3.5     |      | V  |  |
| $t_{rr}$           | reverse recovery time                     | $V_{GS} = -5 V; I_F = 40 A$<br>$V_R = 800 V; -di_F/dt = 1000 A/\mu s$ |      | 55      |      | ns |  |
| $Q_{RM}$           | reverse recovery charge (intrinsic diode) |                                                                       |      | 285     |      | nC |  |
| $I_{RM}$           | max. reverse recovery current             |                                                                       |      | 15      |      | A  |  |

**Note:**

When using SiC Body Diode the maximum recommended  $V_{GS} = -5V$

| Package SMPD   |                                |                                    | Ratings |              |           |        |
|----------------|--------------------------------|------------------------------------|---------|--------------|-----------|--------|
| Symbol         | Definitions                    | Conditions                         | min.    | typ.         | max.      |        |
| $I_{RMS}$      | RMS current                    | wide terminal<br>standard terminal |         |              | 100<br>60 | A<br>A |
| $T_{stg}$      | storage temperature            |                                    | -55     |              | 150       | °C     |
| $T_{op}$       | operation temperature          |                                    | -55     |              | 150       | °C     |
| $T_{vj}$       | virtual junction temperature   |                                    | -55     |              | 175       | °C     |
| <b>Weight</b>  |                                |                                    |         | 8            |           | g      |
| $F_c$          | mounting force with clip       |                                    | 40      |              | 130       | N      |
| $d_{Spp/App}$  | creepage distance on surface / | terminal to terminal               | 1.6     |              |           | mm     |
| $d_{Spb/Appb}$ | striking distance through air  | terminal to backside               | 4.0     |              |           | mm     |
| $V_{ISOL}$     | isolation voltage              | $t = 1$ second<br>$t = 1$ minute   |         | 3000<br>2500 |           | V<br>V |



**Part number**

M = Mosfet  
 C = SiC MOSFET  
 B = Generation 2  
 30 = Current Rating [A]  
 P = Phase leg  
 1200 = Reverse Voltage [V]  
 LB = SMPD-B


| Ordering    | Part Name        | Marking on Product | Delivering Mode | Base Qty | Ordering Code    |
|-------------|------------------|--------------------|-----------------|----------|------------------|
| Standard    | MCB30P1200LB-TUB | MCB30P1200LB       | Tube            | 20       | MCB30P1200LB-TUB |
| Alternative | MCB30P1200LB-TRR | MCB30P1200LB       | Tape&Reel       | 200      | MCB30P1200LB-TRR |







**Outlines SMPD-B**

Dimensions in mm (1 mm = 0.0394")


**Notes:**

- 1) potrusion may add 0.2 mm max. on each side
- 2) additional max. 0.05 mm per side by punching misalignment or overlap of dam bar or bending compression
- 3) DCB area 10 to 50  $\mu\text{m}$  convex; position of DCB area in relation to plastic rim:  $\pm 25 \mu\text{m}$  (measured 2 mm from Cu rim)
- 4) terminal plating: 2 - 6  $\mu\text{m}$  Ni + 10 - 25  $\mu\text{m}$  Sn (gal v.) cutting edges may be partially free of plating



**Curves**

 Fig. 1 Typical output characteristics ( $-25^\circ\text{C}$ )

 Fig. 2 Typical output characteristics ( $25^\circ\text{C}$ )

 Fig. 3 Typical output characteristics ( $150^\circ\text{C}$ )

 Fig. 4  $R_{DS(on)}$  normalized vs. junction temperature  $T_{VJ}$ 

 Fig. 5  $R_{DS(on)}$  versus drain current

 Fig. 6  $R_{DS(on)}$  versus junction temperature  $T_{VJ}$


**Curves**


Fig. 7 Norm. breakdw  $V_{DSS}$  & treshhold voltage  $V_{TH}$  versus junction temperature  $T_{VJ}$




Fig. 8 Typical transfer characteristics




Fig. 9 Typical forward transconductance




Fig. 10 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $-55^{\circ}\text{C}$




Fig. 11 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $25^{\circ}\text{C}$




Fig. 12 Forward voltage drop of intrinsic diode versus  $V_{DS}$  measured at  $150^{\circ}\text{C}$


**Curves**


Fig. 13 Typical switching energy versus drain current




Fig. 14 Typical switching energy versus temperature




Fig. 15 Typical switching energy versus external gate resistor




Fig. 16 Typical switching time versus external gate resistor




Fig. 17 Typical turn on gate charge, trendline




Fig. 18 Typical transient thermal impedance