








	PCB PREFERABLY CHAMFERED
	SLOT. THICK. . FOR SIDE KEYING
	SIDE KEYING. THICK. ON LAST CAVITY. THICKNESS 0.7mm
5	WIRE RANG: 0.22-0.35mm ² SEE APPLICATION SPEC. 114-18467
	IEC60695-2-11 / IEC60335-1 GLOW WIRE TEST 750 °C WITHOUT FLAME
	X..CAVITY LOADED WITH CONTACT O..CAVITY WITHOUT CONTACT
2	MATING PART: PCB (WITH FRAMES ACC. RAST 2.5 E.G. PN 964 575/576 TAB HEADER (FOR EXAMPLE: X-1971921/922-Y)
	KEYING RIBS: CUTTING WITH TERMINATION MACHINE POSSIBLE

OTHER NOTE SEE SHEET 3 OF 3.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. Karabiyik 24MAY2002		 TE Connectivity			
DIMENSIONS:		CHK B. Schnaubel 24MAY2002					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED		NAME AMP DUOPLUG 2.5 MARK II FEMALE CONNECTOR 3-20 POSITION SELECTIVE LOADED			
		APVD T. Klennor 24MAY2002					
		PRODUCT SPEC 108-18785					
		APPLICATION SPEC 114-18467					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		A1	00779	©=1534798	-
Customer Drawing				SCALE	5:1	SHEET	1 of 4 REV
				073			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. Karabiyik CHK B. Schnaubelt APVD T. Klenner		24MAY2002 24MAY2002 24MAY2002		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP DUOPLUG 2.5 MARK II FEMALE CONNECTOR 3-20 POSITION SELECTIVE LOADED		SIZE CASE CODE DRAWING NO RESTRICTED TO	
mm	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±1°	PRODUCT SPEC 108-18785 APPLICATION SPEC 114-18467					
	FINISH	WEIGHT					
MATERIAL				A1		00779	C=1534798 SCALE 10:1 SHEET 3 OF 3 REV 073
-	-	Customer Drawing					

