



SANYO Semiconductors

DATA SHEET

LV762XXX Series

Bi-CMOS IC

For NTSC/PAL/SECAM Color TVs

Built-in CTV Microcontroller

**Video and Sound Processing ICs
(VIF/SIF/Y/C/Deflection/CbCr IN)**

Overview

The LV762XXX series is a single-chip video and sound processor IC with a built-in microcontroller that supports all of the NTSC, PAL and SECAM broadcasting systems. The IC provides fully integrated solution to rationalize the design of color TV sets, increase productivity, and reduce total costs.

Functions

- I²C bus control system with a built-in microcontroller
- VIF/SIF/Y/C/Deflection/CbCr IN
- Adjustment-free VIF/SIF
- 1X'tal multi-system that supports NTSC, PAL and SECAM broadcasting systems
- No VCO coil required
- Internal sound carrier BPF, 4-system sound carrier trap
- Digital AFT system

■ Any and all SANYO Semiconductor Co.,Ltd. products described or contained herein are, with regard to "standard application", intended for the use as general electronics equipment (home appliances, AV equipment, communication device, office equipment, industrial equipment etc.). The products mentioned herein shall not be intended for use for any "special application" (medical equipment whose purpose is to sustain life, aerospace instrument, nuclear control device, burning appliances, transportation machine, traffic signal system, safety equipment etc.) that shall require extremely high level of reliability and can directly threaten human lives in case of failure or malfunction of the product or may cause harm to human bodies, nor shall they grant any guarantee thereof. If you should intend to use our products for applications outside the standard applications of our customer who is considering such use and/or outside the scope of our intended standard applications, please consult with us prior to the intended use. If there is no consultation or inquiry before the intended use, our customer shall be solely responsible for the use.

■ Specifications of any and all SANYO Semiconductor Co.,Ltd. products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

SANYO Semiconductor Co., Ltd.

www.semiconductor-sanyo.com/network

LV762XXX Series

Lineup

Type No.	SECAM	Tone/Surround	E/W	Teletext	ROM
LV762102F					Flash 64K(P:48K,GC:16K)
LV762102C					MASK 64K(P:48K,GC:16K)
LV762113F			○		Flash 128K(P:96K,GC:32K)
LV762113C			○		MASK 128K(P:96K,GC:32K)
LV762133F		○	○		Flash 128K(P:96K,GC:32K)
LV762133C		○	○		MASK 128K(P:96K,GC:32K)
LV762213F	○		○		Flash 128K(P:96K,GC:32K)
LV762213C	○		○		MASK 128K(P:96K,GC:32K)
LV762232F	○	○	○		Flash 64K(P:48K,GC:16K)
LV762232C	○	○	○		MASK 64K(P:48K,GC:16K)
LV762233F	○	○	○		Flash 128K(P:96K,GC:32K)
LV762233C	○	○	○		MASK 128K(P:96K,GC:32K)
LV76233N5F	○	○	○	○	Flash 192K(P:140K,GC:52K)

Specifications

Maximum Ratings (BIP Chip) at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Maximum supply voltage	V ₆₂ max		6.0	V
	V ₄ max		6.0	V
Maximum supply current	I _g max		15	mA
	I ₂₀ max		20	mA
	I ₄₉ max		26.5	mA
Allowable power dissipation	P _d max	Ta ≤ 65°C *	1.3	W
Operating temperature	T _{opr}		-10 to +65	°C
Storage temperature	T _{stg}		-55 to +150	°C

* Mounted on a substrate: 230mm×150mm×1.6mm, glass epoxy board.

Absolute Maximum Ratings (Micro-computer Chip) at Ta = 25°C, V_{SS} = 0V

Parameter		Symbol	Pins	Conditions	Ratings			Unit
					min	typ	max	
Maximum supply voltage		V _{DD} max	CpuV _{DD}		-0.3		+6.0	V
Input voltage		V _I	XT1, RES		-0.3		V _{DD} +0.3	V
Output voltage		V _O (1)	XT2, FILT		-0.3		V _{DD} +0.3	V
		V _O (2)	CpuV _{DD} 2		-0.3		3.3V+0.3	V
Input/output voltage		V _{IO}	Ports0, 1		-0.3		V _{DD} +0.3	V
High level output current	Peak output current	I _{OPH}	Ports04 to 07, 1	•CMOS output •For each pin.	-10			mA
	Mean output current	I _{OMH}	Ports04 to 07, 1	•CMOS output •For each pin.	-1			mA
	Total output current	ΣI _{OA} H	Ports04 to 07, 1	The total of all pins.	-25			mA
Low lever output current	Peak output current	I _{OPL}	Ports0, 1	For each pin			20	mA
	Mean output current	I _{OML} (1)	P02, P03, P06, P07 Ports1	For each pin			1	mA
		I _{OML} (2)	P00, P01, P04, P05	For each pin			8	mA
	Toral output current	ΣI _{OA} L(1)	P02, P03, P06, P07 Ports1	The total of all pins.			45	mA
		ΣI _{OA} L(2)	P00, P01, P04, P05	The total of all pins.			16	mA

LV762XXX Series

Operating Conditions (BIP Chip) at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Recommended supply voltage	V ₆₂		5.0	V
	V ₄		5.0	V
Recommended supply current	I _g		11	mA
	I ₂₀		13	mA
	I ₄₉		22	mA
Operating supply voltage range	V ₆₂		4.7 to 5.3	V
	V ₄		4.7 to 5.3	V
Operating supply current range	I _g		9 to 13	mA
	I ₂₀		11 to 15	mA
	I ₄₉		20.5 to 26.5	mA

Recommended Operating Range (Micro-computer Chip) at Ta = -10°C to +65°C, V_{SS} = 0V

Parameter	Symbol	Pins	Conditions	V _{DD} [V]	Ratings			Unit
					min	typ	max	
Operating supply voltage	V _{DD}	CpuV _{DD}	0.229μs ≤ t _{CYC} ≤ 200μs		4.5		5.5	V
Hold voltage	V _{HD}	CpuV _{DD}	RAMs and the registers data are kept in HOLD mode.		2.0		5.5	V
High level input voltage	VIH (1)	Ports0, 1, P00 port input /interrupt		4.5 to 5.5	0.3V _{DD} +0.7		V _{DD}	V
	VIH (2)	Port00 Watch-dog timer		4.5 to 5.5	0.9V _{DD}		V _{DD}	V
	VIH (3)	RES		4.5 to 5.5	0.75V _{DD}		V _{DD}	V
Low level input voltage	VIL (1)	Ports0, 1, P00 port input /interrupt		4.5 to 5.5	V _{SS}		0.1V _{DD} +0.4	V
	VIL (2)	Port00 Watch-dog timer		4.5 to 5.5	V _{SS}		0.15V _{DD} +0.4	V
	VIL (3)	RES		4.5 to 5.5	V _{SS}		0.25V _{DD}	V
Operation cycle time (*1)	t _{CYC} (1)		All functions operating	4.5 to 5.5		0.231		μs
	t _{CYC} (2)		OSD and Data slicer are not operating	4.5 to 5.5	0.231		200	μs
Oscillation frequency range	FmVCO1		Built-in VCO1 Oscillation System clock	4.5 to 5.5		13.0		MHz
	FmVCO1 (*2)		Built-in VCO2 oscillation OSD clock	4.5 to 5.5		12.5		MHz
						16.6		MHz
	FmRC		Built-in RC oscillation	4.5 to 5.5	0.3	1.0	2.0	MHz
	FsX'tal	XT1 (P07) XT2 (P06)	At the 32.768KHz crystal Oscillating See the figure 1	4.5 to 5.5		32.768		kHz
Oscillation stabilizing time	tmsVCO		•after the HOLD mode •Power-On	4.5 to 5.5		300		mS

(Note) FLASH-ROM erase/write temperature range : Ta = 25±2°C (V_{DD} = 4.5 to 5.5V)

(*1) Relational expression between t_{CYC} and oscillation frequency ;

1/1 frequency dividing : 3/FmVCO1, 1/2 frequency dividing : 6/FVCO1.


(*2) OCKSEL is the selectable register for OSD clock frequency. (See the LC873200 users manual for details.)

LV762XXX Series


Package Dimensions

unit : mm (typ)

3300



Block Diagram



- SANYO Semiconductor Co.,Ltd. assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all SANYO Semiconductor Co.,Ltd. products described or contained herein.
- SANYO Semiconductor Co.,Ltd. strives to supply high-quality high-reliability products, however, any and all semiconductor products fail or malfunction with some probability. It is possible that these probabilistic failures or malfunction could give rise to accidents or events that could endanger human lives, trouble that could give rise to smoke or fire, or accidents that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all SANYO Semiconductor Co.,Ltd. products described or contained herein are controlled under any of applicable local export control laws and regulations, such products may require the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written consent of SANYO Semiconductor Co.,Ltd.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the SANYO Semiconductor Co.,Ltd. product that you intend to use.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.
- Upon using the technical information or products described herein, neither warranty nor license shall be granted with regard to intellectual property rights or any other rights of SANYO Semiconductor Co.,Ltd. or any third party. SANYO Semiconductor Co.,Ltd. shall not be liable for any claim or suits with regard to a third party's intellectual property rights which has resulted from the use of the technical information and products mentioned above.

This catalog provides information as of May, 2009. Specifications and information herein are subject to change without notice.