

CATALOG LISTING

1EN118-6

PAGE 1 OF 1

ISSUE

5

REVISIONS

A PR 20292 TSM 14 DEC 92

B CO94194 DLT 8 MAR 99

C 201294 GJW 26 SEP 00

RASTER

DRAWN

T S M 14DEC92





CHECK

D A W 14 DEC 92


CHECK

RELEASE NO. PR-20292

REPLACES



- NOTES
- 1 — CORROSION RESISTANT STEEL ENCLOSURE
 - 2 — SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 — COINCIDENCE OF OPERATING AND RELEASING POINTS: .004 OF PLUNGER TRAVEL
 - 4 — CIRCUIT DIAGRAM, CATALOG LISTING, FED. MFG. CODE AND DATE CODE ARE PERMANENTLY MARKED ON SIDE OF HOUSING
 - 5 — HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 6 — RATING APPLIES TO CIRCUIT 1-2-3
 - 7 — RATING APPLIES TO CIRCUIT 4-5-6
 - 8 — REPLACEMENT MOUNTING HARDWARE — PACKET 19PA8
 - 9 — PLUNGER SEAL MATERIAL — FLOUROSILICONE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH					THIRD ANGLE PROJECTION 		
CHARACTERISTICS		ELECTRICAL DATA				SCALE FULL	
OPERATING FORCE — — — — 6-12 LB		CONTACT ARRANGEMENT 2X S P D T				DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE --- 30 LB MAX		28 VDC				UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 4 LB MIN							
PRETRAVEL — — — — .040 MAX		LOAD	7 SEA LEVEL 6 7 50,000 FT. 6				ONE PLACE (.0) ±.030
DIFFERENTIAL TRAVEL — — .020 MAX		RES	4	1	4	1	TWO PLACE (.00) ±.015
OVERTRAVEL — — — — .250 MIN		IND	2	.5	2	.5	THREE PLACE (.000) ±.005
		MOTOR	4				ANGLES ±
							WEIGHT .46 LB MAX

ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN118-6](#)