



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Wire-to-Wire**
Compatible Insulation Diameter (Max): **2.9 mm [.115 in]**
Compatible Insulation Diameter Range: **2.9 mm [.115 in]**
Lead Wire Size: **.3 - .8 mm²**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire & Lead Wire
------------------------------------	-------------------------

Contact Features

Magnet Wire Terminal Type	Wire-to-Wire
Terminal Plating Material	Unplated
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Barbs
-----------------------	-------

Dimensions

Terminal Height	3.17 mm[.125 in]
Compatible Insulation Diameter (Max)	2.9 mm[.115 in]
Compatible Insulation Diameter Range	2.9 mm[.115 in]
Lead Wire Size	.3 - .8 mm²
Magnet Wire Size	.16 - 1.02 mm



Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Product Length	7.62 mm[.3 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 - 175 °C[-40 - 347 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 8-1601046-1
331-101-000=WIRE2WIRE,STD,SMZ

TE Part # 6-1601046-2
WIRE2WIRE,STD,SMZ

TE Part # 1601046-3
STANDARD WIRE TO WIRE SIAMEZE,
HIGH TEMP,

TE Part # 4-1601056-1
031-119-000=WIRE2WIRE,STD,SMZ

TE Part # 4-1601117-1
WIRE2WIRE,FINE,SMZ

TE Part # 8-1601046-2
331-101-000=WIRE2WIRE,STD,SMZ

TE Part # 1601433
531-101-002= POCKET
SPECIFICATION

Also in the Series | SIAMEZE

Insertion & Extraction Tools(1)

Magnet Wire Terminals(192)

Customers Also Bought

TE Part # DT04-2P
REC, 2P, GRY, N

TE Part # W2S
Wedgelocks: DEUTSCH DT

TE Part # 0460-202-16141
DEUTSCH Solid Contacts

TE Part # 282104-1
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

TE Part # DT06-2S
PLG, 2P, GRY, N

TE Part # 281934-2
SINGLE WIRE SEAL

TE Part # 114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



Documents

Product Drawings

031-101-000=WIRE2WIRE,STD,SMZ

English

031-101-000=WIRE2WIRE,STD,SMZ

English

CAD Files

Customer View Model

ENG_CVM_CVM_4-1601046-1_H.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1601046-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1601046-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Magnet Wire Terminals & Splices

English

1-1773702-7 _IDC_Magnet_Wire

English

Product Specifications

Application Specification

English