

SMA CONNECTORS



TE CONNECTIVITY (TE)

2037 8125 92

AMP | SM , SMA

1052201-1

TE Internal Number: 1052201-1

Mil-Spec: M39012/56-3125

Alias ID: 2037-8125-92

Always EU RoHS/ELV Compliant

Applies To **Coaxial Cable**

Panel Mount **Without**

Body Material **Stainless Steel**

Body Plating Finish **Passivated**

50 Ohm **Yes**

✓ Active

 **PRODUCT DRAWING**
English

Product Drawings

SMA RIGHT ANGLE CABLE PLUG-CRIMP ATTACHMENT (M39012/56-3125) CAT C

PDF ([TIFF AVAILABLE](#))

English

SMA RIGHT ANGLE CABLE PLUG-CRIMP ATTACHMENT (M39012/56-3125) CAT C

PDF ([TIFF AVAILABLE](#))

English

Instruction Sheets

Instruction Sheet (U.S.)

SMA Right-Angle Cable Plugs

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Applies To

Coaxial Cable

RF Connector Type

SMA

Connector Style

Plug

Cable Type

RG 178, RG 196

Product Type

Connector - RF

Shrink Tubing

Without

Retractable Collar

Without

Dielectric Material

PTFE Fluorocarbon

Configuration Features

Snap-Lock

Without

Electrical Characteristics	50 Ohm	Yes
	75 Ohm	No
Signal Characteristics	Frequency (GHz)	12.4
Body Features	Body Material	Stainless Steel
	Body Plating Finish	Passivated
	Body Style	Right Angle
	Gasket Material	Silicone Rubber
	Ferrule Material	Brass, Copper
Contact Features	Captivation Method	Mechanical
	Center Contact Plating Material	Gold
	Center Contact	With
	Center Contact Material	Brass
	Captivated Contacts	With
Termination Features	Cable Termination Type	Crimp
Mechanical Attachment	Panel Mount	Without
	Safety Wire Holes	Without
	Coupling Nut Material	Stainless Steel
Dimensions	Length	34.93 mm [1.375 in]
Industry Standards	Military Category	C
Packaging Features	Packaging Method	Package
Product Compliance	Statement of Compliance PDF	VIEW ALL PRODUCT COMPLIANCE