



Sensors > Pressure Sensors > Pressure Transducers



Pressure Sensor Type: Industrial Pressure Transducer

Pressure: 206.84 bar [3000 psi]

Pressure Type: Absolute

Supply Voltage Range: 9 - 30 V

Output Signal Type: 4 - 20 mA

Features

Product Type Features

Pressure Sensor Type	Industrial Pressure Transducer
Pressure Type	Absolute

Configuration Features

Electrical Connection	Packard
-----------------------	---------

Electrical Characteristics

Supply Voltage Range	9 - 30 V
----------------------	----------

Dimensions

Hex Width Across Flats	24 mm[.944 in]
Product Height	57.15 mm[2.25 in]

Usage Conditions

Pressure	206.84 bar[3000 psi]
Operating Temperature Range	-40 - 125 °C[-40 - 257 °F]

Operation/Application

Proof Pressure Range	3X Rated
Output Signal Type	4 - 20 mA
Pressure Accuracy	±0.1% FSO

Other

Sensor Options	Adhesive Label, No Snubber
----------------	----------------------------



Port Fitting

1/4 MNPT

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # U5354-000002-002BA
[PRESS XDCR U5354-000002-002BA](#)



TE Part # U5354-000002-014BA
[PRESS XDCR U5354-000002-014BA](#)

Also in the Series | MEAS U5300



Pressure Transducers(5)

Customers Also Bought



TE Part # 1-6609021-2
Single Phase Filters, Corcom B Series



TE Part # 0460-215-1631
PIN, SOLID, SIZE 16, 14AWG, AU



TE Part # 34163
TERMINAL,PG R 16-14 5/16



TE Part # 4-2176094-0
RP 2A 0.25W 309K 0.1% 25PPM 1K RL



TE Part # 3-2176093-2
RP 2A 0.25W 20K 0.1% 25PPM 1K RL



TE Part # 5-2176403-5
3550 180R 1%



TE Part # 2-2176328-3
CRGP 1206 680R 1%



TE Part # NB09542001
ATUM-16/4-0-STK



TE Part # 6-1437558-8
MTE106D=(MSTE) SW TOG
WATERPRO

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_U5354-000005-03KPA_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_U5354-000005-03KPA_H.3d_igs.zip



English
Customer View Model
[ENG_CVM_CVM_U5354-000005-03KPA_H.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[U5300](#)
English