

CA-07S1N8A6Z00 - Device connector front mounting



1619897

<https://www.phoenixcontact.com/us/products/1619897>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, Axial seal, Central fastening Pg13,5, coding: N

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1619897
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAEL
Catalog page	Page 94 (C-2-2019)
GTIN	4046356820691
Weight per piece (including packing)	23.8 g
Weight per piece (excluding packing)	23.8 g
Customs tariff number	85366990
Country of origin	DE

CA-07S1N8A6Z00 - Device connector front mounting

1619897

<https://www.phoenixcontact.com/us/products/1619897>



Technical data

Product properties

Product type	Circular connectors (device side)
Data management status	
Article revision	05

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 2 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	7
Direction of rotation	Standard
Connection profile	7
Contact diameter Signal contacts	2 mm
Litz wire cross-section Signal contacts min.	1 mm ²
Litz wire cross-section Signal contacts max.	2.5 mm ²
Nominal current per signal contact	20 A
Rated voltage Signal contact	48 V AC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	If necessary, order locking nut separately
Housing material	CuZn
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

CA-07S1N8A6Z00 - Device connector front mounting


1619897

<https://www.phoenixcontact.com/us/products/1619897>



Drawings

Dimensional drawing



Installation dimensions


CA-07S1N8A6Z00 - Device connector front mounting

1619897

<https://www.phoenixcontact.com/us/products/1619897>



Schematic diagram



Connector pin assignment

CA-07S1N8A6Z00 - Device connector front mounting

1619897

<https://www.phoenixcontact.com/us/products/1619897>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619897>

cUL Recognized				
Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	10 A	14 - 14	-

UL Recognized				
Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	17 A	14 - 14	-

cULus Recognized

CA-07S1N8A6Z00 - Device connector front mounting

1619897

<https://www.phoenixcontact.com/us/products/1619897>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-07S1N8A6Z00 - Device connector front mounting

1619897

<https://www.phoenixcontact.com/us/products/1619897>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com