



Connectors > Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage**

Sealable: **No**

Circuit Application: **Signal**

Number of Ports: **4**

Port Matrix Configuration: **1 x 4**

Features

Product Type Features

|                            |           |
|----------------------------|-----------|
| Cage Type                  | Ganged    |
| Pluggable I/O Product Type | Cage      |
| Sealable                   | No        |
| Form Factor                | QSFP28/56 |

Configuration Features

|                                     |       |
|-------------------------------------|-------|
| Number of Rear EONs per Port Column | 1     |
| Number of Ports                     | 4     |
| Port Matrix Configuration           | 1 x 4 |

Contact Features

|                                               |     |
|-----------------------------------------------|-----|
| PCB Contact Termination Area Plating Material | Tin |
|-----------------------------------------------|-----|

Termination Features

|                                             |                          |
|---------------------------------------------|--------------------------|
| Termination Post & Tail Length              | 2.2 mm[.086 in]          |
| Termination Method to Printed Circuit Board | Through Hole - Press-Fit |

Dimensions

|                             |                  |
|-----------------------------|------------------|
| PCB Thickness (Recommended) | 1.45 mm[.057 in] |
|-----------------------------|------------------|

Operation/Application

|                            |                             |
|----------------------------|-----------------------------|
| Pluggable I/O Applications | SFP+ Stacked Belly-to-Belly |
|----------------------------|-----------------------------|



|                      |        |
|----------------------|--------|
| Heat Sink Compatible | Yes    |
| Circuit Application  | Signal |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                  |            |
|------------------|------------|
| Packaging Method | Box & Tray |
|------------------|------------|

Other

|                              |                         |
|------------------------------|-------------------------|
| Included Lightpipe           | No                      |
| EMI Containment Feature Type | Customer Applied Gasket |

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2024 (240)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



|                                                                                                                                                                      |                                                                                                                                                                        |                                                                                                                                                                       |                                                                                                                                                                      |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # CAT-C11-Z806726<br/>QSFP28 to QSFP28 Cable Assembly:<br/>30 AWG</p>   |  <p>TE Part # CAT-C11-N49<br/>QSFP28-Two QSFP28 Cable<br/>Assembly: 30 AWG</p>       |  <p>TE Part # CAT-C11-Z8<br/>QSFP28 to QSFP28 Cable Assembly:<br/>26 AWG</p>       |  <p>TE Part # CAT-C11-N490333<br/>QSFP28-Four SFP+ Cable Assembly:<br/>30 AWG</p> |
|  <p>TE Part # CAT-C11-N490325<br/>QSFP28-Four SFP+ Cable Assembly:<br/>26 AWG</p>  |  <p>TE Part # CAT-Q17-N490325<br/>QSFP56 to QSFP56 Cable Assembly:<br/>30 AWG</p>   |  <p>TE Part # CAT-Q17-N49033<br/>QSFP56-Two QSFP56 Cable<br/>Assembly: 30 AWG</p> |  <p>TE Part # CAT-C11-Q17<br/>QSFP56 to QSFP56 Cable Assembly:<br/>26 AWG</p>    |
|  <p>TE Part # CAT-Q17-N49011<br/>QSFP56-Four SFP56 Cable Assembly:<br/>30 AWG</p> |  <p>TE Part # CAT-Q17-N490333<br/>QSFP56-Four SFP56 Cable Assembly:<br/>26 AWG</p> |  <p>TE Part # 1888810-2<br/>EMI/Dust Cover,XFP And QSFP</p>                      |  <p>TE Part # 1551920-2<br/>zQSFP+ connector assembly</p>                       |

Also in the Series | [zQSFP+/QSFP28](#)

|                                                                                                          |                                                                                                                                |                                                                                                                                       |
|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
|  <p>Heat Sinks(7)</p> |  <p>Pluggable I/O Cable Assemblies(81)</p> |  <p>Pluggable IO Connectors &amp; Cages(425)</p> |
|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|

Customers Also Bought

|                                                                                                                                              |                                                                                                                                                   |
|----------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 2309409-1<br/>DDR4 SODIMM 260P 5.2H STD</p> |  <p>TE Part # 2227249-2<br/>1x4 Cage Assy Bhnd Bzl QSFP28</p> |
|----------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|



Documents

Product Drawings

1x4 Cage Assy, Bhnd Bezel, QSFP28

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2227250-1\_A\_c-2227250-1-a.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2227250-1\_A\_c-2227250-1-a.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2227250-1\_A\_c-2227250-1-a.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications

Application Specification

English