


COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_BMA-50-0-1/119_N

Properties

- Offers a range of floating configurations
- High reliability and ease of assembly
- Intermatable with the OSP connectors series
- Applicable in frequencies up to 18 GHz



Product configuration

Interface type	Gender	Standard
BMA	jack	IEC 60169-33_MIL-STD-348A/321

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0038 kg
Mating cycles	1000
Flange type	square flange / 12.7 X 12.7
Tab style	Standard

Environmental data

Operation temperature	-65 °C ... 125°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22645624	23_BMA-50-0-1/119_NE	Single

**COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel receptacle, jack (female),
flange mount**

23_BMA-50-0-1/119_N

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2750 / Date of publication: 26.11.2023 / uncontrolled copy