

AV1610R612R04

✓ ACTIVE

Alcoswitch | Alcoswitch AV16

TE Internal #: 2213774-7

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Anti-Vandal, Single Actuator, Flush Actuator Profile, Alcoswitch AV16

[View on TE.com >](#)



Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Anti-Vandal**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal
Illuminated	With
Actuator Style	Round

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Momentary

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage Range	36 VDC



Body Features

Actuator Force	458.9 g[16.18 oz]
Case Material	PBT
Product Orientation	Vertical
Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

Housing Features

Process Sealed	Yes
----------------	-----

Dimensions

	16 in
--	-------

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213775-1 AV16 SPM 0.4VA POWER LED WHITE 12V	TE Part # 2213775-3 AV16 SPM 0.4VA POWER LED RED 12V	TE Part # 2213775-5 AV16 SPM 0.4VA POWER LED YELLOW 12V	TE Part # 2213775-7 AV16 SPM 0.4VA POWER LED GREEN 12V
TE Part # 2213775-9 AV16 SPM 0.4VA POWER LED BLUE 12V	TE Part # 2213774-1 AV16 SPM 0.4VA FIX RING LED WHITE 12V	TE Part # 2342832-2 AVC16L FLAT AIO RED R 500MM/2X3	TE Part # 2342832-1 AVC16L FLAT AIO RGB R 500MM/2X3
TE Part # 2342833-2 AVC16L FLAT AIO RED RL 500MM/2X3	TE Part # 2342833-1 AVC16L FLAT AIO RGB RL 500MM/2X3	TE Part # 2342832-4 AVC16L FLAT S04 RED R 500MM/2X3	TE Part # 2342832-3 AVC16L FLAT S04 RGB R 500MM/2X3
TE Part # 2342833-4 AVC16L FLAT S04 RED RL 500MM/2X3	TE Part # 2342833-3 AVC16L FLAT S04 RGB RL 500MM/2X3	TE Part # 2342832-6 AVC16L FLAT S16 RED R 500MM/2X3	TE Part # 2342832-5 AVC16L FLAT S16 RGB R 500MM/2X3




TE Part # 2342833-6
AVC16L FLAT S16 RED RL 500MM/2X3



TE Part # 2342833-5
AVC16L FLAT S16 RGB RL 500MM/2X3



TE Part # 2342832-7
AVC16M FLAT AIO RGB R 500MM/2X3



TE Part # 2342833-7
AVC16M FLAT AIO RGB RL 500MM /2X3

Also in the Series | Alcoswitch AV16




Push Button Switches(21)

Customers Also Bought



TE Part # 9-188275-0
MICRO-MATCH SMD FTE



TE Part # 3-640443-2
02P MTA100 CONN ASSY GRN



TE Part # 1-2007492-8
SFP+assy2x1 EMI Sprg No Lp Sn Enhanced




TE Part # 1761681-3
IDC LOW PRO HDR 10P VERT HT BLACK




TE Part # 2299940-2
ZQSFP+ STACKED REC ASSEMBLY 2X1,HS




TE Part # 1-770968-0
04P MINI UMN L R/A HDR ASSY SN




TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # 2274845-1
CFP2 RECEPTACLE ASSEMBLY



TE Part # 7-2176370-9
RQ 0603 2K8 0.1% 10PPM 5K RL



TE Part # 384265-E
STVB/2 32 M AB VV 4-00 0606 * * 247 E007



Documents

Product Drawings

AV16 SPM 0.4VA FIX RING LED GREEN 12V

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213774-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213774-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213774-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch flyer

English