




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **8**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	2

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Operating Voltage	125 VAC

Body Features

Connector Profile	Standard
-------------------	----------



Primary Product Color	Black
Contact Features	
Contact Mating Area Length	4 mm[.157 in]
Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	2 µm[78.74 µin]
Contact Layout	Inline
Contact Underplating Material Thickness	.5 µm[19.69 µin]
PCB Contact Termination Area Plating Material Finish	Bright
Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Brass
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.38 µm[14.96 µin]
Contact Type	Pin
Contact Current Rating (Max)	2 A
Termination Features	
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Post & Tail Length	2.8 mm[.11 in]
Termination Method to Printed Circuit Board	Through Hole - Solder
Housing Features	
Centerline (Pitch)	2 mm[.079 in]
Housing Material	PA9T GF
Dimensions	
Connector Length	8 mm[.315 in]
Connector Width	4 mm[.157 in]
Row-to-Row Spacing	2 mm[.079 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Usage Conditions	
Housing Temperature Rating	High
Operating Temperature Range	-40 - 125 °C[-40 - 257 °F]
Operation/Application	



Assembly Process Feature	Without Pick and Place Cover
Circuit Application	Signal

Industry Standards

UL Rating	Recognized
Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag, Box
------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2316108-8
8P,2MM,REC,HSG,DR,CRIMP,PLAIN,BOX



TE Part # 2307730-8
8P,2MM,B-B,REC,DRHZ,SMD,0.38AU,TR



TE Part # 2307719-8
8P,2MM,B-B,REC,DRHZ,2.8,0.38AU,TB




TE Part # 2314925-8
8P,2MM,B-B,REC,DRHZ,2.8,0.38AU,TR



TE Part # 2314845-8
8P,2MM,BB,REC,DRV,T,SMD,AU.38,TB,W/CP




TE Part # 2307818-8
8P,2MM,BB,REC,DRV,T,SMD,AU.38,TR,W/CP



TE Part # 2314813-8
8P,2MM,B-B,REC,DRV,T,2.0,0.38AU,TB,W/CAP




TE Part # 2307782-8
8P,2MM,B-B,REC,DRV,T,2.0,0.38AU,TR,W/CAP



TE Part # 2314821-8
8P,2MM,B-B,REC,DRV,T,2.7,0.38AU,TB



TE Part # 2314825-8
8P,2MM,B-B,REC,DRV,T,2.7,0.38AU,TB,W/CAP




TE Part # 2307783-8
8P,2MM,B-B,REC,DRV,T,2.7,0.38AU,TR,W/CAP




TE Part # 2307784-8
8P,2MM,B-B,REC,DRV,T,3.2,0.38AU,TUBE




TE Part # 2314941-8
8P,2MM,B-B,REC,DRHZ,SMD,0.38AU,TB



TE Part # 2314917-8
8P,2MM,B-B,REC,DRHZ,2.1,0.38AU,TB



TE Part # 2307718-8
8P,2MM,B-B,REC,DRHZ,2.1,0.38AU,TR



TE Part # 2307720-8
8P,2MM,B-B,REC,DRHZ,3.4,0.38AU,TUBE



TE Part # 2314853-8
8P,2MM,REC,DRV,T,OTR,2.3,0.38AU,TB,W/CP



TE Part # 2307826-8
8P,2MM,REC,DRV,T,OTR,2.3,0.38AU,TR,W/CP



TE Part # 2314861-8
8P,2MM,B-B,REC,DRV,T,OTR,2.8,AU0.38,TB




TE Part # 2314865-8
8P,2MM,REC,DRV,T,OTR,2.8,AU.38,TB,W/CP

Also in the Series | AMPMODU 2 mm



Connector Contacts(27)



PCB Headers & Receptacles(10387)



Wire-to-Board Connector Assemblies & Housings(202)

Customers Also Bought



TE Part # 66506-3
20 DF PIN



TE Part # 66504-3
20 DF SCKT CONT



TE Part # 211401-7
RECEPT,SZ 13-7,CPC



TE Part # 2842127-8
16P,2MM,BRK HDR,DRVT,2.8,0.38AU, TB



TE Part # 1-2213935-2
SMT TB PERP PLUG, RET, 5.0MM, 12 POS



TE Part # 2842139-3
6P,2MM,BRK HDR,DRVT,2.8,0.38AU, BOX




TE Part # 2842139-8
16P,2MM,BRK HDR,DRVT,2.8,0.38AU, BOX



TE Part # 2842163-3
6P,2MM,BRK HDR,DRRT,2.8,0.38AU, BOX



TE Part # 2842163-5
10P,2MM,BRK HDR,DRRT,2.8,0.38AU, BOX



TE Part # 5-2407269-3
CAP, CPC, SIZE 23 PLUG, RED

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2842139-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2842139-4_A.3d_igs.zip

2842139-4

PCB Mount Header, Vertical, Board-to-Board, 8 Position, 2 mm [.079 in] Centerline, Breakaway, Gold, Through Hole - Solder, Signal, Black, AMPMODU 2 mm



English

Customer View Model

[ENG_CVM_CVM_2842139-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English