

2MM-R-S10-VT-02-F-TB

✓ ACTIVE

AMPMODU | AMPMODU 2 mm


TE Internal #: 1-2314876-0

PCB Mount Receptacle, Vertical, Board-to-Board, 10 Position, 2 mm
[.079 in] Centerline, Gold Flash, Through Hole - Solder, Signal,
Black, AMPMODU 2 mm

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **10**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Loaded Positions	10
PCB Mount Orientation	Vertical
Number of Positions	10
Number of Rows	1

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	650 VAC
Operating Voltage	125 VAC

Body Features

Connector Profile	Standard
Primary Product Color	Black



Contact Features

Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	3 - 5 µm[118.11 - 196.85 µin]
Contact Layout	Inline
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold Flash
Contact Mating Area Plating Material Thickness	.1 µm[3.94 µin]
Contact Type	Socket
Contact Current Rating (Max)	2 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.4 mm[.016 in]
Termination Post & Tail Length	2.7 mm[.106 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2 mm[.079 in]
Housing Material	LCP (Liquid Crystal Polymer)

Dimensions

Connector Length	20 mm[.787 in]
Connector Height	4.5 mm[.18 in]
Connector Width	2 mm[.079 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]



Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-40 - 125 °C[-40 - 257 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

2MM-R-S10-VT-02-F-TB

PCB Mount Receptacle, Vertical, Board-to-Board, 10 Position, 2 mm [.079 in]
Centerline, Gold Flash, Through Hole - Solder, Signal, Black, AMPMODU 2 mm



TE Part # 1-2355045-0
10P,2MM,BRK HDR,SRVT,2.8,0.1AU,TB

TE Part # 1-2842102-0
10P,2MM,BRK HDR,SRVT,SMD,0.1AU,TR W/CAP

TE Part # 1-2355104-0
10P,2MM,BRK HDR,SRVT,2.8,0.1AU,TB W/CAP

TE Part # 1-2355172-0
10P,2MM,BRK HDR,SRVT,2.8,0.1AU,BOX

TE Part # 1-2842110-0
10P,2MM,BRK HDR,SRRT,2.8,0.1AU,TB

TE Part # 1-2842114-0
10P,2MM,BRK HDR,SRRT,2.8,0.1AU,TB W/CAP

TE Part # 1-2842122-0
10P,2MM,BRK HDR,SRRT,2.8,0.1AU,BOX

Also in the Series | AMPMODU 2 mm

Connector Contacts(27)

PCB Headers & Receptacles(10387)

Wire-to-Board Connector Assemblies & Housings(202)

Customers Also Bought

TE Part # 1622820-3
3520 10K 5%

TE Part # 1-84534-2
1.25MM FFC POST PLATED V 12P

TE Part # 3-1416100-2
ST3P3LC4

TE Part # 5406435-1
MJ,LPF,R/A,6P,SHLD,PCB GRD

TE Part # 1-2314821-4
14P,2MM,B-B,REC,DRVVT,2.7,0.38AU,TB


TE Part # 1623257-1
CRG0805 1% 5K1

TE Part # 217225J001
V4-3.0-0-SP-SM

TE Part # LL01-2AA04
LL01 1/4" NPT 48" CABLE 100C

2MM-R-S10-VT-02-F-TB

PCB Mount Receptacle, Vertical, Board-to-Board, 10 Position, 2 mm [.079 in]
Centerline, Gold Flash, Through Hole - Solder, Signal, Black, AMPMODU 2 mm



Documents

Product Drawings

10P,2MM,B-B,REC,SRVT,2.7,0.1AU,TB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2314876-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2314876-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2314876-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU 2mm BOARD-TO-BOARD RECEPTACLES

English

AMPMODU 2mm interconnection system QRG

English

Product Specifications

Application Specification

English