


1340153

<https://www.phoenixcontact.com/us/products/1340153>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial PCB connector, degree of protection: IP20, number of positions: 2, 12 Gbps, material: Metal, connection method: Solder connection, cable outlet: straight, for additional information, see the product range drawing in the Download Center

Your advantages

- Complete documentation saves developers time during design-in
- Ideal for WLAN, Bluetooth, LTE, and 5G signals

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1340153 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AB14 |
| Product key | ABNFBA |
| GTIN | 4063151646073 |
| Weight per piece (including packing) | 6.41 g |
| Weight per piece (excluding packing) | 6.41 g |
| Customs tariff number | 85366910 |
| Country of origin | DE |

CUC-COX-J1M-A/KBS - Coaxial PCB connector



1340153

<https://www.phoenixcontact.com/us/products/1340153>

Technical data

Product properties

| | |
|---------------------|------------------------------|
| Product type | Data connector (device side) |
| Type | Coaxial |
| Number of positions | 2 |
| Connection profile | R-SMA (f) |
| Type of packaging | PE bag |
| Type | Socket |
| Cable outlet | straight |
| Thread type | 1/4-36 UNS |

Data management status

| | |
|------------------|----|
| Article revision | 01 |
|------------------|----|

Electrical properties

| | |
|-----------------------------|-----------------------|
| Rated surge voltage (III/2) | 1500 V |
| Frequency range | 10 Hz |
| Test voltage | 1000 V _{rms} |
| Transmission medium | Copper |

Output data

| | |
|------------------------|----------|
| Transmission frequency | 1.00 GHz |
|------------------------|----------|

Connection data

Connection technology

| | |
|-------------------------------------|-------------------|
| Connection method | Solder connection |
| Locking mechanism tightening torque | 1.10 Nm |

Dimensions

| | |
|------------------|----------|
| Width | 7 mm |
| Length | 19.5 mm |
| Installed height | 10.00 mm |
| Orientation to | 90.00 ° |

Material specifications

| | |
|--|---------|
| Flammability rating according to UL 94 | V0 |
| Housing material | Metal |
| Contact material | CuBe2Pb |
| Contact surface material | NiP-Au |

Cable/line

| | |
|--------------|----|
| Halogen-free | no |
|--------------|----|

CUC-COX-J1M-A/KBS - Coaxial PCB connector



1340153

<https://www.phoenixcontact.com/us/products/1340153>

Mechanical properties

Mechanical data

| | |
|-------------------------------------|---------|
| Insertion/withdrawal cycles | > 100 |
| Extraction force per signal contact | < 20 N |
| Locking mechanism tightening torque | 1.10 Nm |

Environmental and real-life conditions

Test specification

| | |
|---|-----------------|
| Specification | DIN EN 61169-1 |
| Contact resistance R_2 | 2.00 m Ω |
| Insulation resistance, neighboring contacts | 5 G Ω |
| Impulse withstand voltage at sea level | 1400.00 V DC |
| Power-frequency withstand voltage | 1000.00 V AC |

Test specification

| | |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-14 Test Na |
| Cold stress | -10 °C |

Test specification

| | |
|---------------|--------------------------|
| Specification | DIN EN 60068-2-6 Test Fc |
| Frequency | 10-2000-10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.75 mm |
| Acceleration | 100.00 m/s ² |
| Test duration | 2.50 h |

Ambient conditions

| | |
|---|-------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -55 °C ... 125 °C |
| Ambient temperature (storage/transport) | -55 °C ... 125 °C |


Mounting

| | |
|---------------|---------------|
| Mounting type | THR soldering |
|---------------|---------------|

Processing notes

| | |
|--------------------------|-------|
| Process | THR |
| Moisture Sensitive Level | MSL 1 |

Drawings



Classification wave soldering profile

CUC-COX-J1M-A/KBS - Coaxial PCB connector



1340153

<https://www.phoenixcontact.com/us/products/1340153>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440390 |
| ECLASS-12.0 | 27440390 |
| ECLASS-13.0 | 27460201 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-COX-J1M-A/KBS - Coaxial PCB connector



1340153

<https://www.phoenixcontact.com/us/products/1340153>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com