




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 1624 - 4106 CMA

Stud Size: #10

Features

Product Type Features

Terminal Features	Sheared
Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.978 g
----------------	--------

Contact Features

Contact Base Material	Steel
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Nickel



Contact Underplating Material	None
-------------------------------	------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.12 in
Wire Size	1624 - 4106 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.51 mm[.02 in]
Product Length	19.81 mm[.78 in]
Barrel Inside Diameter	2.28 mm, 4.41 mm[.09 in][.174 in]
Compatible Insulation Diameter (Max)	4.45 mm[.175 in]
Compatible Insulation Diameter Range	3.05 - 4.45 mm[.12 - .175 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 - 250 °C[-40 - 482 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1742775-1
RT .129 DIA TERMINAL .062 CABLE ST

TE Part # 1742777-1
RT .262 DIA TERMINAL .062 CABLE ST

TE Part # 2836524-1
OCEAN_2.0_APPLICATOR-E-120F220F-REM

TE Part # 2836524-2
OCEAN_2.0_APPLICATOR-E-120F220F-REA

TE Part # 7-2836524-7
OCEAN_2.0_SPARE_PART_KIT-120F220F

TE Part # 7-2836524-1
OCEAN_2.0_APPLICATOR-E-120F220F

TE Part # 7-2836524-2
OCEAN_2.0_APPLICATOR-E-120F220FA

Customers Also Bought

TE Part # 41531-1
250 FASTON FLAG REC 18-12 AWG NPST

TE Part # 521208-1
POSI-LOK HSG.250-6 POS RAST5

TE Part # 42110-3
RING TERMINAL 18-14 AWG BR

TE Part # 42404-1
250 FASTON FLAG REC 18-12 AWG NPST



TE Part # 1217095-1
RCPT 250 P0S-LOCK 16-12 0126BR

TE Part # 55621-2
TERMINAL R PG 8 1/4

TE Part # 690455-1
FRONT STRIPPER

TE Part # 20005447-00
PRESS XDCR M30J1-000105-100PG

TE Part # 520194K050
RT-3-NO.3-0-0.5IN

TE Part # 1108782-1
MDL2-GR.O-6.B1-3

Documents

Product Drawings
RING TONGUE TERMINAL 18-14 AWG NIPST
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_350199-1_L.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_350199-1_L.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_350199-1_L.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Application Specification
English