

S21MA7-P06MFD0-397S  
medi\_snap  
type\_s2



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S21MA7-P06MFD0-397S |
| Termination       | solder              |
| Size              | 1                   |
| Locking principle | push                |
| Coding            | a_key_medi          |
| Cable Diameter    | cable_medi_39       |
| Cable outlet      | bend_relief         |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.

**CODING:** 40°

**POSITIONS:** 6 Positions

**DIMENSIONS**

The pin layout corresponds to the view on the termination area

Contact insert description

|                      |        |
|----------------------|--------|
| Number of contacts   | 6      |
| Contact type         | pins   |
| Contact diameter     | 07mm   |
| Insulator material   | peek   |
| Wire cross section   | 26_awg |
| Termination          | solder |
| Termination diameter | 065mm  |

reverse\_gender\_on\_request

Technical information

|                                          |          |                       |
|------------------------------------------|----------|-----------------------|
| Max. creepage and air clearance distance | 085_mm   | iec_60601_2mopp_2moop |
| Nominal current single contact           | 06_a     | iec_60512_5_2         |
| Nominal current insert                   | 4,5 A    | vde_0298_4            |
| Test voltage                             | 11_kv_ac | eia_364_20f           |

safety\_text  
iec\_60601\_plug

**Mechanical and environmental data**

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip50     |
| Operating temperature | 50_120_c |
| Mating cycles         | 2000     |

mated\_unmated

**Insulator materials MEDI-SNAP®**

psu\_peek

**Material and surface treatments**

|              |               |
|--------------|---------------|
| Housing      | psu_gray      |
| Color option | gray          |
| Contact      | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text