




SPLICE

TE Internal #: 928782-2  
Crimp Wire Pins, Tabs & Ferrules, Tab, Mating Tab Width .094 in [2.4 mm], Mating Tab Thickness .6 mm [.023 in], 17 - 13 AWG Wire Size, SPLICE  
[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: **Tab**  
Mating Tab Width: **2.4 mm [ .094 in ]**  
Mating Tab Thickness: **.6 mm [ .023 in ]**  
Compatible Insulation Diameter Range: **3.1 mm [ .122 in ]**  
Wire Size: **17 - 13 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
------------------------------------	-----------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Crimp Wire Terminal Type	Tab
Mating Tab Width	2.4 mm[.094 in]
Mating Tab Thickness	.6 mm[.023 in]
Barrel Type	Open
Terminal Plating Material	Tin
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

--	--



Compatible Insulation Diameter Range	3.1 mm[.122 in]
Wire Size	2000 - 5200 CMA
Barrel Inside Diameter	1.8 mm, 2.45 mm[.07 in][.096 in]
Terminal Material Thickness	.6 mm[.023 in]
Overall Product Length	10.76 mm[.423 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2266355-2  
OCEAN-2.0-APPLICATOR-S-130F180F

KIT  
REPRESENTATION ONLY  
TE Part # 7-2266355-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-130F180F

TE Part # 7-2266355-2  
OCEAN-2.0-APPLICATOR-S-130F180FA

Also in the Series | SPLICE

Crimp Wire Pins, Tabs & Ferrules(1)

Splices(64)

Customers Also Bought

TE Part # 953697-2  
MQS, CONNECTOR HOUSING

TE Part # 1379675-5  
12W TAB HSG ASSY NATURAL

TE Part # 343445-2  
AMP-IN MINI (SPECIAL) 18.5-14 AWG

TE Part # 1718762-3  
MCON 1.2 LL TAB SWS AG

TE Part # 1326030-7  
2.8MM RECP,UNSEAL,14-16AWG,REV

TE Part # 2-1703498-1  
2POS, MCON 1.2 LL TAB SEALED COD B

TE Part # 1803018-3  
CRIMPER, INSUL O

TE Part # 7-568176-0  
CRIMPER, WIRE (.050" 'F')

TE Part # CD41583001  
55E0211-0.50-0(B01)

