

1375965-4  ACTIVE

## AMPMODU


TE Internal #: 1375965-4

PC/104 Connectors, 120 Position, .079 in [2 mm] Centerline

[View on TE.com >](#)



Connectors > PCB Connectors > Board-to-Board Connectors > PC/104 Connectors



Number of Positions: 120

Centerline (Pitch): 2 mm [.079 in]

Number of Loaded Positions: 120

Contact Current Rating (Max): 3 A

## Features

### Product Type Features

Connector System	Board-to-Board
------------------	----------------

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

### Configuration Features

Number of Standoffs	2
---------------------	---

Stacking Configuration	Non-Stack Through
------------------------	-------------------

Number of Positions	120
---------------------	-----

Number of Loaded Positions	120
----------------------------	-----

### Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
---------------------------------------	---------

Insulation Resistance	1000 MΩ
-----------------------	---------

### Body Features

Primary Product Color	Black
-----------------------	-------

### Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

Contact Current Rating (Max)	3 A
------------------------------	-----

### Termination Features

Termination Post & Tail Length	2.85 mm [.112 in]
--------------------------------	-------------------

Termination Method to Printed Circuit Board	Through Hole - Solder
---------------------------------------------	-----------------------

### Mechanical Attachment

PCB Mount Retention Type	None
Connector Mounting Type	Board Mount

### Housing Features

Housing Material	Nylon - GF
Centerline (Pitch)	2 mm [.079 in]

### Usage Conditions

Operating Temperature Range	-55 - 105 °C [-67 - 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Assembly Process Feature	Board Standoff
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1375967-4  
PC104 PLUS NONSTK NO STNDOFF

## Customers Also Bought



TE Part # 5747844-6  
09 MSFL RCPT RA 318 (SL,FM,BL)



TE Part # 4-1622820-4  
3520 3K3 5%



TE Part # 350787-3  
02P UMNL PIN HDR ASSY 94VO LF



TE Part # 3-794620-4  
04P MICRO MNL ASSY,R/A,HDR,LF



TE Part # 3-794636-6  
06P MICRO MNL ASSY,VRT,SMT,LF



TE Part # 7-1879214-2  
CPF 0402 2K05 0.1% 25PPM 1K RL



TE Part # 1-2176337-9  
CRGCQ 0402 330R 1%

## Documents

### Product Drawings

[PC104 PLUS NOSTKTHRU 2 STNDOFF](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_1375965-4\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1375965-4\\_D.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1375965-4\\_D.2d\\_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[AMPMODU\\_INTERCONNECTION\\_SYSTEM\\_SECTION1AND2](#)

English

**Product Specifications**

[Application Specification](#)

English

**Agency Approvals**

[UL Report](#)

English