

1415006-1 ACTIVE

SCHRACK | SCHRACK Miniature Relay PT

TE Internal #: 1415006-1

Power Relays, Industrial Panel Plug-In, Monostable, 759 mW Coil

Power Rating DC, 777 Ω Coil Resistance, SCHRACK Miniature Relay

PT

[View on TE.com >](#)



Relays & Contactors > Relays > Power Relays



Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable**

Coil Power Rating DC: **759 mW**

Coil Resistance: **777 Ω**

Coil Special Features: **UL Coil Insulation Class F**

Features

Product Type Features

Relay Type

Industrial Panel Plug-In

Configuration Features

Insulation Special Features

5000V Initial Surge Withstand Voltage
between Contacts & Coil

Coil Special Features

UL Coil Insulation Class F

Contact Arrangement

4 Form C (4 CO)

Contact Number of Poles

4

Electrical Characteristics

Insulation Initial Dielectric Between Contacts & Coil 1200 Vrms

Insulation Initial Dielectric Between Open Contacts 1200 Vrms

Contact Limiting Making Current 12 A

Contact Limiting Short-Time Current 300 A

Insulation Initial Dielectric Between Adjacent Contacts 2500 Vrms

Contact Limiting Breaking Current 6 A

Coil Power Rating DC 759 mW

Coil Resistance 777 Ω

Coil Voltage Rating 24 VDC

Contact Current Rating 6 A

Contact Switching Load (Min)	10mA @ 12V
------------------------------	------------

Contact Switching Voltage (Max)	240 VAC
---------------------------------	---------

Contact Voltage Rating	240 VAC
------------------------	---------

Body Features

Product Weight	30 g[1.058 oz]
----------------	----------------

Contact Features

Contact Material	AgNi90/10
------------------	-----------

Termination Features

Relay Connection Type	Plug-In
-----------------------	---------

Mechanical Attachment

Product Mount Type	Socket
--------------------	--------

Dimensions

Insulation Clearance Between Contact & Coil	3 mm
---	------

Insulation Creepage Between Contact & Coil	4 mm[.157 in]
--	---------------

Product Width	22.5 mm[.885 in]
---------------	------------------

Product Length	28 mm[1.1 in]
----------------	---------------

Product Height	29 mm[1.14 in]
----------------	----------------

Usage Conditions

Environmental Ambient Temperature (Max)	70 °C[158 °F]
---	---------------

Operating Temperature Range	-40 - 70 °C
-----------------------------	-------------

Operation/Application

Actuating System	DC
------------------	----

Indicator Type	LED
----------------	-----

Coil Magnetic System	Monostable
----------------------	------------

Packaging Features

Packaging Method	Carton & Tube
------------------	---------------

Other

Length Class (Mechanical)	25 - 30 mm
---------------------------	------------

Insulation Creepage Class	3 - 5.5 mm
---------------------------	------------

Insulation Clearance Class	2.5 - 4 mm
----------------------------	------------

Height Class (Mechanical)	25 - 30 mm
---------------------------	------------

Coil Power Rating Class	600 - 800 mW
Width Class (Mechanical)	20 - 25 mm
Contact Current Class	5 - 10 A

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts






Also in the Series

SCHRACK Miniature Relay PT



Customers Also Bought



Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_1415006-1_A1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1415006-1_A1.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1415006-1_A1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Miniature Relay PT

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English