

SMT COMMON MODE CHOKES

Military & Aerospace SLIC Series



- Ⓟ *Enhanced SLIC platform*
- Ⓟ *Military/Aerospace Applications*
- Ⓟ *Dielectric strength: 1500VRMS*
- Ⓟ *Designed for DC/DC converters*
- Ⓟ *Storage Temperature: -55°C to +130°C*
- Ⓟ *Lead Finish: Sn63/Pb37*

Electrical Specifications 25°C — Operating Temperature -55°C to +130°C

Part Number	Inductance per Winding (uH ±35%)	Irated (A)	DCR per winding (mΩ MAX)	Curve (see # below)	Package	Weight (grams)	Quantity in Tube	Quantity in Reel
PL8200	470	14	8	9	Big Foot	14.8	15	75
PL8201	630	11.6	10	7	Big Foot	14.3	20	75
PL8202	810	9.7	14	6	Big Foot	13.5	20	75
PL8203	534	7.2	15	8	HCCI-68	7.7	15	100
PL8204	590	5.6	21	7	LCCI-50	5.2	30	200
PL8205	768	4.7	40	6	LCCI-50	4.9	30	200
PL8206	225	3.3	60	5	LCCI-50	4.7	30	200
PL8207	1320	3.3	60	4	LCCI-50	4.6	30	200
PL8208	1470	2.8	80	3	LCCI-50	4.3	30	200
PL8209	880	1.63	110	2	Polecat	1.5	40	500
PL8210	1170	1.22	200	1	Polecat	1.4	40	500
PL8211	10040	1.4	210	10	LCCI-50	4.5	20	200
PL8212	1125	1.8	55	11	Polecat	1.55	40	500
PL8213	800	3	27	12	Polecat	2.46	40	300
PL8214	382.5	3.3	18	13	Polecat	1.71	40	200
PL8215	536	3.8	17.1	14	LCCI-37	2.52	30	200
PL8216	280	4	13.2	15	Polecat	1.6	40	500
PL8217	486	4.2	16	16	LCCI-44LP	2.99	40	300
PL8218	130*	5	6.75	17	Polecat	1.6	40	500
PL8219	96*	6	4.3	18	Polecat	1.7	40	500
PL8220	400	6	9.4	19	LCCI-44LP	3.53	40	200
PL8221	61*	7	2.9	20	Polecat	1.73	40	500
PL8222	484	8	7.7	21	LCCI-50	5.31	30	200
PL8223	1030	9	9.75	22	HCCI-80	14.63	20	75
PL8224	215	10	3.75	23	Makeni	6.26	25	150
PL8225	95	12.5	2.85	24	LCCI-50	4.92	30	200
PL8226	117	14	1.95	25	Makeni	6.38	25	150
PL8227	500	16	3.25	26	HCCI-80	17.85	20	75
PL8228	380	20	3	27	HCCI-80	17.25	20	75









Notes:

1. The current rating (Irated) is based upon the temperature rise of the component and represents the rms current which will cause a typical temperature rise of 55°C with 50LFM forced cooling.
2. The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.
3. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PL8200 becomes PL8200T.)
4. To order RoHS compliant parts, add "NL" to the part number (i.e. PL8200 becomes PL8200NL and PL8200T becomes PL8200NLT)

SMT COMMON MODE CHOKES

Military & Aerospace SLIC Series



Impedance Curves



SMT COMMON MODE CHOKES

Military & Aerospace SLIC Series

Impedance Curves



SMT COMMON MODE CHOKES




Military & Aerospace SLIC Series

Mechanicals

Schematics

LCCI-50, PL8222 & PL8225

LCCI-50





Mechanicals

Schematics

LCCI-44LP

HCCI-80, PL8223




SMT COMMON MODE CHOKES


Military & Aerospace SLIC Series

PoleCat - PL8212, PL8213, PL8214, PL8216, PL8218, PL8219, PL8221

Mechanicals




Schematics



PoleCat Dimensions

Part number	A	B	X	Y	Z
PL8212	12.7	13.2	8.4	10.4	5.6
PL8213	13.0	13.0	8.4	10.4	8.6
PL8214	13.0	13.0	8.4	10.4	5.6
PL8216	13.0	13.0	8.4	10.4	5.6
PL8218	13.2	13.2	8.6	10.7	5.6
PL8219	13.2	13.2	8.6	10.7	5.6
PL8221	13.5	13.5	8.6	10.7	5.6



SMT COMMON MODE CHOKES


Military & Aerospace SLIC Series

Mechanicals

Schematics

HCCI-68

Big Foot




Mechanicals

Schematics

LCCI-37

Makeni



For More Information

Pulse North America Headquarters
Two Pearl Buck Court
Bristol, PA 19007
U.S.A.

Tel: 215 781 6400
Fax: 215 781 6403

Pulse Europe
Zeppelinstrasse 15
71083 Herrenberg
Germany
Tel: 49 7032 7806 0
Fax: 49 7032 7806 12

Pulse China Headquarters
B402, Shenzhen Academy of Aerospace
10th Kejian Road
High-Tech Zone
Shenzhen, PR China
518057
Tel: 86 755 33966678
Fax: 86 755 3966700

Pulse North China
Room 2704/2705
Super Ocean Finance Ctr.
2067 Yan An Road West
Shanghai 200336
China
Tel: 86 21 62787060
Fax: 86 2162786973

Pulse South Asia
135 Joo Seng Road
#03-02
PM Industrial Bldg.
Singapore 368363
Tel: 65 6287 8998
Fax: 65 6287 8998

Pulse North Asia
3F No. 198, Zhongyuan Road
Zhongli City
Taoyuan County (32068)
Taiwan
Tel: 886 3 4356768
Fax: 886 3 4356823

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.