

RC-16P1N121600 - Cable connector



1600520

<https://www.phoenixcontact.com/us/products/1600520>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241217

Commercial data

Item number	1600520
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFA
GTIN	4046356230483
Weight per piece (including packing)	84.25 g
Weight per piece (excluding packing)	84.25 g
Customs tariff number	85366990
Country of origin	DE

RC-16P1N121600 - Cable connector



1600520

<https://www.phoenixcontact.com/us/products/1600520>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Connector

Insulating body

Coding	N
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Contact diameter	1 mm
Litz wire cross-section	0.08 mm ²
Litz wire cross-section	1 mm ²
Rated current	8 A
Rated voltage	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Housing material	Metal
Type of locking	Screw locking mechanism
Pg screw connection	Pg11
Degree of protection (plugged in)	IP65 IP67
Thread type	M23

Environmental and real-life conditions

RC-16P1N121600 - Cable connector



1600520

<https://www.phoenixcontact.com/us/products/1600520>

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-16P1N121600 - Cable connector


1600520

<https://www.phoenixcontact.com/us/products/1600520>



Drawings

Schematic diagram



Connector pin assignment

RC-16P1N121600 - Cable connector



1600520

<https://www.phoenixcontact.com/us/products/1600520>

Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-16P1N121600 - Cable connector



1600520

<https://www.phoenixcontact.com/us/products/1600520>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	48cb04c0-4116-4350-98e7-bfa482cfd167

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com