

RoHS

### SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass





Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds  
(260℃ for 10 seconds)

Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



### Ordering Information

|              |             |               |            |                 |               |                |                                             |                                              |      |
|--------------|-------------|---------------|------------|-----------------|---------------|----------------|---------------------------------------------|----------------------------------------------|------|
| F            | 2           | D             | 2          | 20              | 1             | 5              | 01                                          | X                                            | 0747 |
| 产品类型<br>F=蜂鸣 | 间距<br>2=2.0 | 塑胶高度<br>D=4.3 | 排数<br>2=双排 | 单排PIN数<br>1~40P | 产品形态<br>1=DIP | 塑胶材料<br>5=PA6T | 电镀厚度<br>00=常镀<br>01=1u"<br>02=2u"<br>03=3u" | 包装方式<br>1=管装<br>2=卷装<br>3=盘装<br>4=袋装<br>5=盒装 | 序列号  |

| Dimension antitheses list |    |     |    |     |     |
|---------------------------|----|-----|----|-----|-----|
| ITEM                      | PB | PC  | PW | H   | W   |
| 001                       |    | 2.4 |    | 4.3 | 4.0 |
| 002                       |    |     |    |     |     |

深圳市连盛精密连接器有限公司

PART NO.

1020200209

TITLE:

2.0FH H=4.3 W=4.0 2x20P DIP PC2.4 U型  
AU1U 青铜 PA6T

OPERATION

DRAW

SCALE

FIT

X.X

±0.30

CHECK

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

APPROVE

DIM

TOL

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

A0

2012.07.23

NEW DRAWING

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9