



NOTES

- 1 THE RECOMMENDED CLAMP TORQUE, REF. NO. Ø:0.15 TO 0.2N·m.
LOCTITE 263, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. Ø FROM LOOSENING.
- 2 APPLICABLE CABLE: Ø14±0.3
- 3 ASSEMBLE WITH APPLICABLE CONNECTOR (RM24WTP-**(85)).
** SHOWS NUMBER OF CONTACT, AND MALE OR FEMALE OF CONNECTOR.
- 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE PLEASE CONFIRM BEFORE THE USE.

3	BRASS	NICKEL PLATING			
2	PHOSPHOR BRONZE	NICKEL PLATING	5	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	4	CHLOROPRENE RUBBER (BLACK)	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00002214	DESIGNED HY. KISHI
F	HIROSE ELECTRIC CO., LTD.	APPROVED : HY. KOBAYASHI 18.02.22	DRAWING NO.	EDC-110117-31-00	DATE 18.04.17
		CHECKED : HY. KOBAYASHI 18.02.22	PART NO.	RM24WTP-CPC(14)(31)	
		DESIGNED : HY. KISHI 18.02.21	CODE NO.	CL109-1495-6-31	
		DRAWN : MK. INOUE 18.02.07			1/1