





# REVISIONS AD




| DIMENSIONS ARE IN INCHES |                             | TOLERANCES ARE:             |  | ANGLES<br>± 5° | TITLE:<br>.050 X .050 C.L.<br>4 ROW SOCKET STRIP | DWG NO:<br>FOLC-1XX-X2-XX-Q-XXX-XX<br>SHEET 1 OF 2 |
|--------------------------|-----------------------------|-----------------------------|--|----------------|--------------------------------------------------|----------------------------------------------------|
| ONE PLACE DECIMALS ± .1  | THREE PLACE DECIMALS ± .005 | FOUR PLACE DECIMALS ± .0020 |  |                |                                                  |                                                    |

| FOLC-1XX-X2-XX-Q-XXX-XX          |                                                                            | OPTION                                                                                           |
|----------------------------------|----------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|
| No. OF POSITIONS<br>-05 THRU -50 | LEAD STYLE<br>-02: SURFACE MOUNT<br>-L2: LOW INSERTION FORCE SURFACE MOUNT |                                                                                                  |
| -LC: LOCKING CLIP (FIG: 1)       |                                                                            | -P: PICK AND PLACE PAD (SEE FIG 3, SHT 2)                                                        |
|                                  |                                                                            | -TR: TAPE & REEL                                                                                 |
|                                  |                                                                            | -K: POLYAMIDE FILM PAD (.005 [.13] THICK W/ SILICONE ADHESIVE)(SEE FIG 4, SHT 2) (USE K-500-300) |
|                                  |                                                                            | OPTION                                                                                           |
|                                  |                                                                            | -LC: LOCKING CLIP (SEE FIGURE 1)                                                                 |
|                                  |                                                                            | -LCR: LOCKING CLIP REVERSED (SEE FIG 2, SHT 2)                                                   |
|                                  |                                                                            | BODY SPECIFICATION                                                                               |
|                                  |                                                                            | -Q: 4 ROW                                                                                        |




- NOTES:
1. PARTS TO BE PACKAGED IN TUBES.
  2. ROW TO ROW DIMENSION MUST BE WITHIN .002 OF EACH OTHER
  3. (C) REPRESENTS A CRITICAL DIMENSION
  4. MEASURE AT THE BEND, NOT AT THE TIP OF THE CONTACT
  5. THIS DIMENSION TO BE MEASURED FROM TAIL TO LC.



MATERIAL:  
INSULATOR:  
BLACK LIQUID CRYSTAL POLYMER  
TERMINAL:  
BeCu

PLOT SCALE 1=2

| OPTION            | PACKAGING TUBE | PLUG  |
|-------------------|----------------|-------|
| -LC, -LCR         | PT-1-24-01-55  | TP-24 |
| -P, -P-LC, -P-LCR | PT-1-24-04-38  | TP-03 |
| -K, -K-LC, -K-LCR | PT-1-24-05-38  | TP-03 |



PACKAGING VIEW  
SCALE .75

**samtec**

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150  
PHONE (812) 944-6733 P.O. BOX 1147  
CODE 55322

MADE BY:  
GREG REIDINGER 3-29-93

FOLC-1XX-X2-XX-Q-XXX-XX  
SHEET 1 OF 2

**PROPRIETARY NOTE**  
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.