

1. REPRESENTS A CRITICAL DIMENSION
2. ROW TO ROW DIMENSION MUST BE WITHIN .002 OF EACH OTHER
3. MEASURE AT THE BEND, NOT AT THE TIP OF THE CONTACT
4. THIS DIMENSION TO BE MEASURED FROM TAIL TO LC.
5. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
6. PARTS TO BE PACKAGED IN TUBES.

DO NOT
SCALE FROM
THIS PRINT






FIG 1
FOLC-1XX-XX-X-Q-LC SHOWN
* = -LC DIMENSIONS

FOLC-1XX-X2-XX-Q-XXX-XX

No OF POSITIONS
-05 THRU -50


LEAD STYLE
-02: SURFACE MOUNT
-L2: LOW INSERTION
FORCE SURFACE MOUNT

AG PLATING SPECIFICATION
-S: 30μ" SELECTIVE GOLD ON CONTACT, MATTE TIN TAIL
-H: 30μ" HEAVY GOLD ON CONTACT, 3μ" FLASH GOLD ON TAIL
-L: 10μ" LIGHT GOLD ON CONTACT, MATTE TIN TAIL
-SM: 30μ" SELECTIVE GOLD ON CONTACT, MATTE TIN TAIL


OPTION
-P: PICK AND PLACE PAD (SEE FIG 3, SHT 2)
-TR: TAPE & REEL
-K: POLYIMIDE FILM PAD (.005 [.13] THICK W/ SILICONE ADHESIVE) (SEE FIG 4, SHT 2) (USE K-500-300)

OPTION
-LC: LOCKING CLIP (SEE FIG 1)
-LCR: LOCKING CLIP REVERSED (SEE FIG 2, SHT 2) (SEE NOTE 5)

BODY SPECIFICATION
-Q: 4 ROW



C-69-X (STANDARD INSERTION FORCE)
C-69L-X (LOW INSERTION FORCE)
C-68-X (STANDARD INSERTION FORCE)
C-68L-X (LOW INSERTION FORCE)



SECTION "A"- "A"
SCALE 3 : 1

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 5°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1
INSULATOR: LCP, UL 94 VO
COLOR: BLACK
CONTACT: BeCu

DESCRIPTION:
.050 X .050 CENTERLINE 4 ROW SOCKET STRIP
DWG. NO.
FOLC-1XX-X2-XX-Q-XXX-XX

REVISION AG







FIG 3
-P: PICK AND PLACE PAD
(SAME AS FIG 1 UNLESS OTHERWISE SHOWN) **AG**


NOTE:

"Q" = USE MEASURED
DIMENSION (REF)
"T" = $\{("Q" - .270 [6.89]) / 2\}$
 $\pm .020 [5.1]$






NOTE:

"R" = USE MEASURED
DIMENSION (REF)
"S" = $\{("R" - .2658 [6.75]) / 2\}$
 $\pm .020 [5.1]$



AG IN-PROCESS



PACKAGING VIEW
SCALE 4:1

OPTION	PACKAGING TUBE	PLUG
-LC, -LCR	PT-1-24-01-55	TP-24
-P, -P-LC, -P-LCR	PT-1-24-04-38	TP-03
-K, -K-LC, -K-LCR	PT-1-24-05-38	TP-03

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 4:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.050 X .050 CENTERLINE 4 ROW SOCKET STRIP

DWG. NO.
FOLC-1XX-X2-XX-Q-XXX-XX

BY: G REIDINGER 03-29-1993 SHEET 2 OF 2