

UPC803G2



A certain prescribed period of time has passed since EOL was announced for these products, and production has been discontinued.

Find similar products

- Product Info
- Design Support
- Documentation
- Ordering

Product Spec

Basic Information

Package

Packing

Basic Information	
Star Product	-
Process	Bipolar
Number of Channels	Dual
Dual Supplies (±V) min.	1
Dual Supplies (±V) max.	16
Input Offset Voltage Vio (±mV) max.	15
Supply Current Icc/Idd (mA) max.	5.6
Slew Rate (V/µs) typ.	13
GBA (MHz) Ref. Only	3
Operating Temperature Topr (°C) min.	-40
Operating Temperature Topr (°C) max.	85
Common Mode Input Voltage Range Vicm (Low Side) (V) Ref. Only	V- +2.3
Common Mode Input Voltage Range Vicm (Hi Side) (V) Ref. Only	V+ -0
IN/OUT Full Range	-
Package Type	SOP
Production Status	EOL

Dimensions

Package	
Ordering Part Name	UPC803G2-E1-A UPC803G2-T1-A UPC803G2-A UPC803G2-E2-A
Name	SOP
JEITA code	P-SOP8-0225-1.27
Previous code	S8GM-50-225B-6
Renesas code	PRSP0008DL-A
Terminal count	8
Terminal pitch (mm)	1.27 mm
Dimensions (mm)	4.4x5.2
Mass (g) [TYP.]	0.08
Drawing Link	s8gm-50-225b
Mount pad	fg0001e
Terminal material - Surface	-

Packing		
Container	Tape No dry pack	H7911-1
	Tape Simple pack	H7909-1
	Tape Complete dry pack	H8520
	Tape	H5351-3
	Tube Simple pack	H5681-5
	Tube Complete dry pack	H5681-5
Packing	Tube Simple pack	H7873-1
	Tube Complete dry pack	H7873-1

Need More Help ?

- Contact UsWebsite Feedback
- DistributorsVideos
- Forums

Others

- Using Our Website
- Privacy Policy
- Security Policy
- Trade Compliance Policy
- Sitemap

Follow Us

- Facebook
- YouTube