


## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/09/180 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Product image



Similar to illustration

Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
- Flange with screw (F)
- Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.

### General ordering data

|              |                                                                                                                                  |
|--------------|----------------------------------------------------------------------------------------------------------------------------------|
| Type         | BCZ 3.81/09/180 SN GN BX                                                                                                         |
| Order No.    | <a href="#">1871380000</a>                                                                                                       |
| Version      | PCB plug-in connector, female plug, 3.81 mm, No. of poles: 9, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box |
| GTIN (EAN)   | 4032248449989                                                                                                                    |
| Qty.         | 50 pc(s).                                                                                                                        |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 16                                                        |
| Packaging    | Box                                                                                                                              |

## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/09/180 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Technical data

#### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 34.38 mm | Width (inches)  | 1.354 inch |
| Height     | 11.1 mm  | Height (inches) | 0.437 inch |
| Depth      | 16.1 mm  | Depth (inches)  | 0.634 inch |
| Net weight | 7.14 g   |                 |            |

#### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

#### system parameters

|                                              |                                     |                                            |                   |
|----------------------------------------------|-------------------------------------|--------------------------------------------|-------------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81 | Type of connection                         | Field connection  |
| Wire connection method                       | Clamping yoke connection            | Pitch in mm (P)                            | 3.81 mm           |
| Pitch in inches (P)                          | 0.15 inch                           | Conductor outlet direction                 | 180°              |
| No. of poles                                 | 9                                   | L1 in mm                                   | 30.48 mm          |
| L1 in inches                                 | 1.2 inch                            | Number of rows                             | 1                 |
| Pin series quantity                          | 1                                   | Rated cross-section                        | 1 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              | Touch-safe protection acc. to DIN VDE 0470 | IP 20             |
| Volume resistance                            | 6.00 mΩ                             | Can be coded                               | Yes               |
| Stripping length                             | 7 mm                                | Tightening torque, min.                    | 0.2 Nm            |
| Tightening torque, max.                      | 0.25 Nm                             | Clamping screw                             | M 2               |
| Screwdriver blade                            | 0.4 x 2.5                           | Screwdriver blade standard                 | DIN 5264          |
| Plugging cycles                              | 25                                  | Plugging force/pole, max.                  | 7 N               |
| Pulling force/pole, max.                     | 5 N                                 |                                            |                   |

#### Material data

|                                       |                           |                                       |                     |
|---------------------------------------|---------------------------|---------------------------------------|---------------------|
| Insulating material                   | PA 66 GF 30               | Colour                                | green               |
| Colour chart (similar)                | RAL 6032                  | Insulating material group             | II                  |
| CTI                                   | ≥ 550                     | Insulation strength                   | ≥ 10 <sup>8</sup> Ω |
| UL 94 flammability rating             | V-0                       | GWFI                                  | 960 °C              |
| Contact material                      | Copper alloy              | Contact surface                       | tinned              |
| Layer structure of plug contact       | 0.5-1.5 µm Cu / 2-5 µm Sn | Storage temperature, min.             | -25 °C              |
| Storage temperature, max.             | 55 °C                     | Max. relative humidity during storage | 80 %                |
| Operating temperature, min.           | -50 °C                    | Operating temperature, max.           | 120 °C              |
| Temperature range, installation, min. | -25 °C                    | Temperature range, installation, max. | 120 °C              |

#### Conductors suitable for connection

|                                                                     |                      |
|---------------------------------------------------------------------|----------------------|
| Clamping range, min.                                                | 0.08 mm <sup>2</sup> |
| Clamping range, max.                                                | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.                             | AWG 28               |
| Wire connection cross section AWG, max.                             | AWG 16               |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                                             | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                                          | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                      |
| w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm <sup>2</sup> max. |                      |

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/09/180 SN GN BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

w. wire end ferrule, DIN 46228 pt 1, min 0.2 mm<sup>2</sup>

w. wire end ferrule, DIN 46228 pt 1, 1.5 mm<sup>2</sup>  
max.

Plug gauge in accordance with EN 60999 a x b; ø 2.4 mm x 1.5 mm ; 2.4 mm

|                     |                                        |                  |                      |      |
|---------------------|----------------------------------------|------------------|----------------------|------|
| Clampable conductor | Cross-section for conductor connection | Type             | fine-wired           |      |
|                     |                                        | nominal          | 0.5 mm <sup>2</sup>  |      |
|                     | AEH                                    | Stripping length | nominal              | 6 mm |
|                     | Cross-section for conductor connection | Type             | fine-wired           |      |
|                     |                                        | nominal          | 0.75 mm <sup>2</sup> |      |
|                     | AEH                                    | Stripping length | nominal              | 6 mm |
|                     | Cross-section for conductor connection | Type             | fine-wired           |      |
|                     |                                        | nominal          | 1 mm <sup>2</sup>    |      |
|                     | AEH                                    | Stripping length | nominal              | 6 mm |
|                     | Cross-section for conductor connection | Type             | fine-wired           |      |
|                     |                                        | nominal          | 1.5 mm <sup>2</sup>  |      |
|                     | AEH                                    | Stripping length | nominal              | 7 mm |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P).

Max. clamping range 1.5 mm<sup>2</sup>

**Rated data acc. to IEC**

tested acc. to standard

IEC 60664-1, IEC 61984

|                                                                           |        |
|---------------------------------------------------------------------------|--------|
| Rated current, max. no. of poles (Tu=20°C)                                | 17.5 A |
| Rated current, max. no. of poles (Tu=40°C)                                | 15.2 A |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V  |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV |

Rated current, min. no. of poles (Tu=20°C) 17.5 A

Rated current, min. no. of poles (Tu=40°C) 17 A

Rated voltage for surge voltage class / pollution degree II/2 320 V

Rated voltage for surge voltage class / pollution degree III/3 160 V

Rated impulse voltage for surge voltage class/ pollution degree III/2 2.5 kV

Short-time withstand current resistance 3 x 1s with 76 A

**Rated data acc. to CSA**

Institute (CSA)



Certificate No. (CSA)

200039-1121690

|                                   |                                                                        |
|-----------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / CSA) | 300 V                                                                  |
| Rated current (Use group B / CSA) | 8 A                                                                    |
| Wire cross-section, AWG, min.     | AWG 28                                                                 |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |        |
|-----------------------------------|--------|
| Rated voltage (Use group C / CSA) | 50 V   |
| Rated current (Use group C / CSA) | 8 A    |
| Wire cross-section, AWG, max.     | AWG 16 |

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/09/180 SN GN BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Rated data acc. to UL 1059**

Institute (cURus)



Certificate No. (cURus)

E60693

Rated voltage (Use group B / UL 1059) 300 V

Rated current (Use group B / UL 1059) 10 A

Wire cross-section, AWG, min. AWG 28

Reference to approval values  
Specifications are maximum values, details - see approval certificate.

Rated voltage (Use group D / UL 1059) 300 V

Rated current (Use group D / UL 1059) 10 A

Wire cross-section, AWG, max. AWG 16

**Packing**

|           |       |            |        |
|-----------|-------|------------|--------|
| Packaging | Box   | VPE length | 40 mm  |
| VPE width | 95 mm | VPE height | 140 mm |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC002637    | ETIM 5.0   | EC002637    |
| ETIM 6.0   | EC002638    | eClass 6.2 | 27-26-07-04 |
| eClass 7.1 | 27-44-04-02 | eClass 8.1 | 27-44-04-02 |
| eClass 9.0 | 27-44-03-09 | eClass 9.1 | 27-44-03-09 |

**Notes**

Notes

IPC conformity  
 Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

**Approvals**

Approvals



ROHS

Conform

## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/09/180 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads


|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">CB Certificate</a><br><a href="#">CB Testreport</a><br><a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Brochure/Catalogue                          | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a> |
| Engineering Data                            | <a href="#">WSCAD</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Engineering Data                            | <a href="#">STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |

## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/09/180 SN GN BX


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Drawings


### Dimensional drawing




### Graph



### Graph



### Graph



The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.




© Weidmüller Interface GmbH & Co. KG

Dimensions without tolerances are no check dimensions




The English version is binding

10




BCZ 3.81/.../180 ...



BCZ 3.81/.../180LR ...



BCZ 3.81/.../180F ...



KUNDENZEICHNUNG  
CUSTOMER DRAWING

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

GENERAL TOLERANCE:  
DIN ISO 2768-m



Max. nos.

98178/5  
16.10.17 MA\_J 01  
Modification

**Weidmüller**

Cat.no.: .

**C 40383**

10

Drawing no. Issue no.  
Sheet 01 of 06 sheets



|             | Date       | Name   |
|-------------|------------|--------|
| Drawn       | 21.02.2006 | GU_D   |
| Responsible |            | MA_J   |
| Checked     | 16.10.2017 | ZHOU_N |
| Approved    |            | XU_S   |

Scale: 2/1

Supersedes: .

**BCZ 3.81/.../180 SN ...**  
BUCHSENLEISTE  
SOCKET BLOCK

Product file: BCZ 3.81

7070

|    |         |           |
|----|---------|-----------|
| 20 | 72.39   | 2.850     |
| 19 | 68.58   | 2.700     |
| 18 | 64.77   | 2.550     |
| 17 | 60.96   | 2.400     |
| 16 | 57.15   | 2.250     |
| 15 | 53.34   | 2.100     |
| 14 | 49.53   | 1.950     |
| 13 | 45.72   | 1.800     |
| 12 | 41.91   | 1.650     |
| 11 | 38.10   | 1.500     |
| 10 | 34.29   | 1.350     |
| 9  | 30.48   | 1.200     |
| 8  | 26.67   | 1.050     |
| 7  | 22.86   | 0.900     |
| 6  | 19.05   | 0.750     |
| 5  | 15.24   | 0.600     |
| 4  | 11.43   | 0.450     |
| 3  | 7.62    | 0.300     |
| 2  | 3.81    | 0.150     |
| N  | L1 [mm] | L1 [inch] |