


Home > Products > Relays > Product Feature Selector > Product Details

JMGAC-6MW Product Details

 Share

 Print

 Email



Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- MGA .100 Grid Relay Series
- Input Voltage = 6 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 1 A
- Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

JMGAC-6MW
(1-1617145-7)

TE Internal Number: 1-1617145-7

 Active

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
Product Drawings: - None Available Catalog Pages/Data Sheets: RELAY (PDF, English) Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: Product Line Information Related Products: Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - MOSFET Driver = Without Mechanical Attachment: - Mounting Options = PC Board Electrical Characteristics: - Input Voltage (VDC) = 6 - Contact - Rated Current (A) = 1 - Coil Suppression Diode = Without - Coil Polarity Protection Diode = Without - Coil - Resistance (Ω) = 98 - Coil Power Measurement = Milliwatts - Coil - Rated Power, DC (mW) = 367 - Actuating System = DC - Shock = 75 G's, 6ms - Vibration = 30G's, 10 to 3000Hz Termination Features: - Termination Type = Long Leads Body Features: - Enclosure Type = Hermetically Sealed	Contact Features: - Pin Configuration = .175" Dia. Mounting Pad Configuration Features: Contact - Arrangement = 2 Form C, DPDT, 2 C/O - Coil - Magnetic System = Non Polarized, Monostable - Transistor Driver = Without Industry Standards: - Government/Industry Qualification = Yes - Government/Industry Part Number = M39016/17-038M RoHS/ELV Compliance = Not ELV/RoHS compliant Lead Free Solder Processes = Not suitable for lead free processing - Approved Standards = M39016 Qualified, M Level Conditions for Usage: - Temperature Range (°C) = -65 - +125 Other: Series = MGA .100 Grid Relay - Brand = CII

