


SMA CONNECTORS



TE CONNECTIVITY (TE)

2034 8007 92

AMP | SMA

1051982-1

TE Internal Number: 1051982-1

Mil-Spec: M39012/59-3007

Alias ID: 2034-8007-92

Always EU RoHS/ELV Compliant

Applies To **Coaxial Cable**

Panel Mount **With**

Body Material **Stainless Steel**

Body Plating Finish **Passivated**

Panel Mount Retention Type **Bulkhead**

✓ Active

 **PRODUCT DRAWING**
English

Product Drawings

SMA BULKHEAD FEEDTHRU CABLE JACK-SOLDER ATTACHMENT (M39012/59-3007) CAT A

PDF ([TIFF AVAILABLE](#))

English

SMA BULKHEAD FEEDTHRU CABLE JACK-SOLDER ATTACHMENT (M39012/59-3007) CAT A

PDF ([TIFF AVAILABLE](#))

English

Instruction Sheets

Instruction Sheet (U.S.)

SMA Bulkhead Feedthrough Cable Jack Solder Attachments 1051981-1 And 1051982-1

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Applies To

Coaxial Cable

RF Connector Type

SMA

Connector Style

Jack

Cable Type

RG 174, RG 188, RG 188A, RG 316

Product Type

Connector - RF

Shrink Tubing

Without

Dielectric Material

PTFE

Retractable Collar

Without

Grade

Military

	Sealed	Panel
Configuration Features	Snap-Lock	Without
Electrical Characteristics	50 Ohm	Yes
	75 Ohm	No
	Impedance (Ω)	50
Signal Characteristics	Frequency (GHz)	12.4
Body Features	Body Material	Stainless Steel
	Body Plating Finish	Passivated
	Body Style	Straight
	Gasket Material	Silicone Rubber
	Ferrule Material	Copper Alloy
	Ferrule Plating Material	Gold
Contact Features	Captivation Method	Mechanical
	Center Contact Plating Material	Gold
	Center Contact	With
	Center Contact Material	Beryllium Copper
	Captivated Contacts	With
Termination Features	Cable Termination Type	Solder
Mechanical Attachment	Panel Mount	With
	Panel Mount Retention Type	Bulkhead
	Lockwasher Plating Finish	Passivated
	Polarized	No
	Lockwasher Material	Stainless Steel
	Panel Attachment Style	Rear Mount
	Mounting Nut Material	Stainless Steel
Dimensions	Length	24.39 mm [.96 in]
Industry Standards	Military Category	A

Packaging Features

Packaging Method

Package

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)