

Article No. : 6SL3230-2YH44-0CP0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

#### Input

|                      |                           |                 |
|----------------------|---------------------------|-----------------|
| Number of phases     | 3 AC                      |                 |
| Line voltage         | 500 ... 690 V +10 % -20 % |                 |
| Line frequency       | 47 ... 63 Hz              |                 |
| <b>Rated voltage</b> | <b>690V IEC</b>           | <b>600V NEC</b> |
| Rated current (LO)   | 97.00 A                   | 97.00 A         |
| Rated current (HO)   | 85.20 A                   | 85.20 A         |

#### Output

|                                     |                 |                               |
|-------------------------------------|-----------------|-------------------------------|
| Number of phases                    | 3 AC            |                               |
| <b>Rated voltage</b>                | <b>690V IEC</b> | <b>600V NEC <sup>1)</sup></b> |
| Rated power (LO)                    | 90.00 kW        | 100.00 hp                     |
| Rated power (HO)                    | 75.00 kW        | 75.00 hp                      |
| Rated current (LO)                  | 100.00 A        | 100.00 A                      |
| Rated current (HO)                  | 80.00 A         | 80.00 A                       |
| Rated current (IN)                  | 103.00 A        |                               |
| Max. output current                 | 135.00 A        |                               |
| Pulse frequency                     | 2 kHz           |                               |
| Output frequency for vector control | 0 ... 200 Hz    |                               |
| Output frequency for V/f control    | 0 ... 550 Hz    |                               |

#### Overload capability

|                    |  |
|--------------------|--|
| Low Overload (LO)  | 110% base load current IL for 60 s in a 300 s cycle time       |
| High Overload (HO) | 150% x base load current IH for 60 s within a 600 s cycle time |

### General tech. specifications

|                                   |   |
|-----------------------------------|---|
| Power factor $\lambda$            | 0.90 ... 0.95                             |
| Offset factor $\cos \phi$         | 0.99                                      |
| Efficiency $\eta$                 | 0.98                                      |
| Sound pressure level (1m)         | 72 dB                                     |
| Power loss <sup>3)</sup>          | 1.820 kW                                  |
| Filter class (integrated)         | RFI suppression filter for Category C3    |
| EMC category (with accessories)   | Category C3                               |
| Safety function "Safe Torque Off" | without SIRIUS device (e.g. via S7-1500F) |

### Communication

|               |             |
|---------------|-------------|
| Communication | PROFIBUS DP |
|---------------|-------------|

### Inputs / outputs

#### Standard digital inputs

|                        |       |
|------------------------|-------|
| Number                 | 6     |
| Switching level: 0 → 1 | 11 V  |
| Switching level: 1 → 0 | 5 V   |
| Max. inrush current    | 15 mA |

#### Fail-safe digital inputs

|        |   |
|--------|---|
| Number | 1 |
|--------|---|

#### Digital outputs

|                                    |                |
|------------------------------------|----------------|
| Number as relay changeover contact | 2              |
| Output (resistive load)            | DC 30 V, 5.0 A |
| Number as transistor               | 0              |

#### Analog / digital inputs

|            |                        |
|------------|------------------------|
| Number     | 2 (Differential input) |
| Resolution | 10 bit                 |

#### Switching threshold as digital input

|       |       |
|-------|-------|
| 0 → 1 | 4 V   |
| 1 → 0 | 1.6 V |

#### Analog outputs

|        |                         |
|--------|-------------------------|
| Number | 1 (Non-isolated output) |
|--------|-------------------------|

#### PTC/ KTY interface

|  |
|--|
| 1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5$ °C |
|--|

### Closed-loop control techniques

|   |     |
|---|-----|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC)       | Yes |
| V/f ECO linear / square-law               | Yes |
| Sensorless vector control                 | Yes |
| Vector control, with sensor               | No  |
| Encoderless torque control                | No  |
| Torque control, with encoder              | No  |

## Data sheet for SINAMICS G120X


Article No. : 6SL3230-2YH44-0CP0

| Ambient conditions          |  |
|-----------------------------|--|
| Standard board coating type | Class 3C3, according to IEC 60721-3-3: 2002                    |
| Cooling                     | Air cooling using an integrated fan                            |
| Cooling air requirement     | 0.153 m <sup>3</sup> /s (5.403 ft <sup>3</sup> /s)             |
| Installation altitude       | 1,000 m (3,280.84 ft)  |
| Ambient temperature         |  |
| Operation                   | -20 ... 45 °C (-4 ... 113 °F)                                  |
| Transport                   | -40 ... 70 °C (-40 ... 158 °F)                                 |
| Storage                     | -25 ... 55 °C (-13 ... 131 °F)                                 |
| Relative humidity           |  |
| Max. operation              | 95 % At 40 °C (104 °F), condensation and icing not permissible |

| Connections                    |   |
|--------------------------------|---|
| Signal cable                   |   |
| Conductor cross-section        | 0.15 ... 1.50 mm <sup>2</sup><br>(AWG 24 ... AWG 16)            |
| Line side                      |   |
| Version                        | M10 screw   |
| Conductor cross-section        | 35.00 ... 2 x 120.00 mm <sup>2</sup><br>(AWG 1 ... AWG 2 x 4/0) |
| Motor end                      |   |
| Version                        | M10 screw   |
| Conductor cross-section        | 35.00 ... 2 x 120.00 mm <sup>2</sup><br>(AWG 1 ... AWG 2 x 4/0) |
| DC link (for braking resistor) |   |
| PE connection                  | M10 screw   |
| Max. motor cable length        |   |
| Shielded                       | 150 m (492.13 ft)   |

| Mechanical data           |   |
|---------------------------|---|
| Degree of protection      | IP20 / UL open type   |
| Frame size                | FSF   |
| Net weight                | 68 kg (149.91 lb)   |
| Dimensions                |   |
| Width                     | 305 mm (12.01 in)   |
| Height                    | 709 mm (27.91 in)   |
| Depth                     | 369 mm (14.53 in)   |
| Standards                 |   |
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH        |
| CE marking                | EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC |

| Converter losses to IEC61800-9-2*                    |        |
|--|--------|
| Efficiency class                                     | IE2    |
| Comparison with the reference converter (90% / 100%) | 37.0 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 550V-600V

<sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

## Data sheet for SINAMICS G120X

Article No. : 6SL3230-2YH44-0CP0

### Operator panel: Basic Operator Panel (BOP-2)

#### Screen

Display design LCD, monochrome

#### Mechanical data

Degree of protection IP55 / UL type 12

Net weight 0.140 kg (0.31 lb)

#### Dimensions

Width 70.00 mm (2.76 in)

Height 106.85 mm (4.21 in)

Depth 19.60 mm (0.77 in)

#### Ambient conditions

##### Ambient temperature

Operation 0 ... 50 °C (32 ... 122 °F)

Storage -40 ... 70 °C (-40 ... 158 °F)

Transport -40 ... 70 °C (-40 ... 158 °F)

##### Relative humidity at 25°C during

Max. operation 95 %

#### Approvals

Certificate of suitability CE, cULus, EAC, KCC, RCM