

VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141
<https://www.phoenixcontact.com/us/products/1405141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 4, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, color: silver, PROFINET

Commercial data

Item number	1405141
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
Catalog page	Page 359 (C-2-2019)
GTIN	4046356325929
Weight per piece (including packing)	70.5 g
Weight per piece (excluding packing)	70.5 g
Customs tariff number	85366990
Country of origin	DE

VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.2 Connectors for Outside Environment (Balanced cabling) and chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	--

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	PROFINET
Number of positions	4
Connection profile	RJ45 8(4)
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Data management status

Article revision	17
------------------	----

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage U_N	48 V
Contact resistance	0.001 Ω (Wire – IDC) 0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Connection data

Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
Conductor cross section	0.13 mm ² ... 0.32 mm ² (solid) 0.14 mm ² ... 0.36 mm ² (flexible)

Dimensions

VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

Width	22 mm
Height	30 mm
Length	72 mm

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	CuZn

Cable/line

External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 45 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141
<https://www.phoenixcontact.com/us/products/1405141>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45
connector



1405141
<https://www.phoenixcontact.com/us/products/1405141>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	290a0695-ad91-4dda-acc9-838b8742ba2e

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com