




Features

- Up to 2 lines protects
- Junction capacitance (Max value:18pF)
- Peak Pulse current (8/20 μ s) MAX: 4A
- IEC61000-4-2 (ESD) $\pm$ 30kV (air), $\pm$ 30kV (contact)
- Low leakage current
- Working voltages:36V
- RoHS Compliant

Mechanica Characteristics

- Package: SOT-23
- Lead Finish:Matte Tin
- Case Material: "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Tape Reel :3000pcs

Appearance & Symbo



DB2= Marking Code

Applications

- Automotive Applications
- CAN Bus
- Electronic Control Units
- Body Control Units
- ADAS Control Units
- PowerTrain Control Units

Absolute Maximum Ratings (T=25°C, RH=45%-75%, unless otherwi

Parameters	Symbol	Value	Unit
Peak Pulse Power (tp=8/20μs waveform)	P _{PP}	300	W
Peak Pulse Current (8/20μs)	I _{PP}	4	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V _{ESD}	±30 ±30	KV
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Electrical Characteristics (T=25°C, RH=45%-75%, unless otherwise noted

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V _{RWM}				36	V
Reverse Breakdown Voltage	V _{BR}	I _R = 1mA	40		45	V
Reverse Leakage Current	I _R	V _R = 36V			1	uA
Clamping voltage	V _C	I _{PP} = 1A, T _P =8/20us			60	V
Clamping voltage	V _C	I _{PP} =4A, T _P =8/20us			75	V
Junction capacitance	C _J	V _R =0V, f =1MHz			18	pF

Typical Characteristics

FIG1: Power rating derating curve




FIG2: pulse Waveform




FIG3: Capacitance between terminals characteristics






FIG4: Clamping Voltage vs. Peak Pulse Current




Soldering parameters

Reflow Condition		Pb-Free assembly see as bellow
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L) (Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C




Package mechanical data



Symbol	Dimensional	
	Millimeters	
	min	max
A	0.9	1.15
A1	0	0.1
A2	0.9	1.05
a	(0.6)	
D	2.8	3.0
E	1.2	1.4
E1	2.25	2.55
e	(0.95)	
e1	1.8	2.0
b	0.3	0.5
c	0.08	0.15
L	(0.55)	
L1	0.3	0.5
θ	0°	8°

Suggested Land Pattern



Symbol	Dimensional
	Millimeters
X	(0.6)
Y	(0.8)
Z	(2.02)
P	(1.9)