

AR0221

CMOS Image Sensor, 2.1 MP, 1/1.7"

Product Overview

For complete documentation, see the data sheet.

ON Semiconductor AR0221 is a 1/1.7-inch CMOS digital image sensor with an active-pixel array of 1928 (H) × 1088 (V). This advanced image sensor captures images in either linear or high dynamic range, with rolling-shutter readout. It includes sophisticated camera functions such as in-pixel binning, windowing and both video and single frame modes. AR0221 is optimized for both low light and high dynamic range scene performance with 4.2um BSI pixels. The sensor includes flexible functions such as in-pixel binning, windowing, and both video and single frame modes. The device is programmable through a simple two-wire serial interface, and supports both MIPI and HiSPi output interfaces.

Features

- 2.1Mp at 60 fps for Excellent Video Performance
- Optical Format (1/1.7inch)
- 1080p Mode for 16:9 Video
- Superior Lowlight Performance
- 4.2um large Back Side Illuminated Pixel Technology
- Supports Line Interleaved T1/T2/T3 Readout to Enable HDR Processing in ISP Chip at 1080P and 30fps
- Onchip Phaselocked Loop (PLL) Oscillator
- Integrated Color and Lens Shading Correction
- Slave Mode for Precise Framerate Control
- Data Interfaces: - 4-lane MIPI CSI-2 and HiSpi SLCS

For more features, see the data sheet




Applications

- Video Surveillance
- High Dynamic Range Imaging

End Products

- Security Camera
- Action camera
- Car DVR
- Body camera

Part Electrical Specifications

| Product | Status | Compliance | Type | Megapixels | Frame Rate (fps) | Optical Format | Shutter Type | Pixel Size (µm) | Output Interface | Color | Package Type | Case Outline | MSL Type | MSL Temp (°C) | Container Type | Container Qty. |
|-----------------------------|----------|---|------|------------|------------------|----------------|---|-----------------|------------------|-------|--------------|--------------|----------|---------------|----------------|----------------|
| AR0221SR2C00 SUEA0-DPBR | Active |  | CMOS | 2.1 | 60 | 1/2 inch | Electronic Rolling and Global Reset Release | 4.2 x 4.2 | Multi | RGB | IBGA-87 | 503 BR.PDF | 4 | 260 | JTRAY | 2160 |
| AR0221SR2C00 SUEA0-DPBR1 | Obsolete |  | CMOS | 2.1 | 60 | 1/2 inch | Electronic Rolling and Global Reset Release | 4.2 x 4.2 | Multi | RGB | IBGA-87 | 503 BR.PDF | 4 | 260 | JTRAY | 216 |
| AR0221SR2C00 SUEA0-DRBR | Active |  | CMOS | 2.1 | 60 | 1/2 inch | Electronic Rolling and Global Reset Release | 4.2 x 4.2 | Multi | RGB | IBGA-87 | 503 BR.PDF | 4 | 260 | JTRAY | 2160 |