






2366066-1 SHOWN AS

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE DRAWING	15JAN2020	V.T	I.Y
	A1	REVISE	15JAN2021	S.Z	I.Y
	B	REVISED PER PCN :E-21-004518	16APR2021	S.Z	Z.Z
	B1	REVISE ECN-22-186969	28NOV2022	W.W	Z.Z



NOTES:

DETAIL A
SCALE 10:1

- 1 ASSEMBLY PN AND PART REVISION:
2366066-X A
X: X=1, 2, 3, 4 FOR VARIOUS CODE.
A: PART REVISION, DETAIL SEE TABLE ON THE DRAWING SHEET 1.

2. MATERIAL: SEE DRAWING TABLE

- 3 INEDTIFICATION FOR CABLE PINOUT.

- 4 THE ASSEMBLY DATE CODE: INDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
SUCH AS :18C1411
18: YEAR, FIRST AND SECOND DIGITS (18=2018)
C: MONTH, THIRD DIGIT , EXCLUDING "1" , A=JAN, B=FEB, C=MARCH...H=AUGUST,J=SEPTEMBER...
14: DAY, FOURTH AND FIFTH DIGITS(14=14th DAY)
11: HOUR, SIXTH AND SEVENTH DIGITS(11=11AM)

- 5 VERIFY THE SECOND LOCK SEATED ON PRE-LOCK POSITION FOR DELIVERY.
PULL SECOND LOCK TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF SECOND LOCK BEING HIT TO END-LOCK POSITION.

6. APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE SHOWN AS BELOW FOR RECOMMEND,
CONSULT TE CONNECTIVITY FOR MORE APPLICATION INFORMATION.

B1	1418760-1 5-1418760-1	TIN	0.50~0.75	Ø1.40~Ø1.90
	1418762-1	TIN	1.0~1.5	Ø1.90~Ø2.40
	TERMINAL PN	TERMINAL PLATING	WIRE SIZE (MM2)	INSULATION WIRES OD(MM)

7.THIS TAB MATES WITH 2366036-X PLUG (X=1, 2, 3, 4 FOR RELEVANT CODE).



CODING A PN:2366066-1	CODING B PN:2366066-2	CODING C PN:2366066-3	CODING D PN:2366066-4

1	1	1	1	YELLOW	PBT-GF30	SECOND LOCK	2
1				BLUE	PA6-GF15	HOUSING.CODE D	1
	1			GREEN	PA6-GF15	HOUSING.CODE C	
		1		GREY	PA6-GF15	HOUSING.CODE B	
			1	BLACK	PA6-GF15	HOUSING.CODE A	
QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO
19.61	19.61	19.61	19.61	WEIGHT OF EACH ASSY NO. (g)			
B	B	B	B	REVISION OF EACH ASSY NO.			
2366066-4	2366066-3	2366066-2	2366066-1	TE ASSEMBLY PN			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TANG 03JAN2020		 TE Connectivity						
DIMENSIONS: mm		CHK E. JIANG 03JAN2020								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L. YIN 03JAN2020		NAME 48POS, MCON 1.2 LL, TAB HSG ASSY UNSEALED, CONNECTOR -					
	0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.100 4 PLC ±0.0500 ANGLES ±5°		PRODUCT SPEC 108-32618							
	MATERIAL		APPLICATION SPEC 114-32365		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
	FINISH		WEIGHT		A2 00779		C=2366066			
		RESTRICTED CUSTOMER				SCALE 2:1		SHEET 1 OF 2		REV B1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

APPLICATION AS SHOWN



SCALE 1:1



NOTES:

8 .48POS.TAB AND PLUG HSG ASSY MATES WITH BULKHEAD BRACKET.


48POS. HSG ASSY P/N: MALE SIDE:2366066-*,FEMALE SIDE:2366036-*,

BULKHEAD BRACKET P/N: 2050752-1 OR FOLLOW DIMENSIONS ON INTERFACE.


IF THERE ARE ANY OTHER APPLICATIONS FOR THIS BRACKET, PLEASE CONFIRM WITH TE PRODUCT ENGINEER FIRST.



BULKHEAD BRACKET INTERFACE



SECTION X-X

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TANG 03JAN2020	 TE Connectivity		
DIMENSIONS: mm		CHK E. JIANG 03JAN2020			
		APVD L. YIN 03JAN2020	NAME 48POS, MCON 1.2 LL, TAB HSG ASSY UNSEALED, CONNECTOR		
		PRODUCT SPEC 108-32618	SIZE -		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-32365	CAGE CODE A2100779	DRAWING NO C-2366066	RESTRICTED TO
MATERIAL -		WEIGHT -	SCALE 2:1		
FINISH -		SHEET 2 OF 2			REV B1
		RESTRICTED CUSTOMER			