

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 6 mm ... 10 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243774

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1619722
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEA
Catalog page	Page 86 (C-2-2019)
GTIN	4046356821957
Weight per piece (including packing)	89.3 g
Weight per piece (excluding packing)	89.3 g
Customs tariff number	85366990
Country of origin	DE

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Technical data

Notes

Order information:	Order crimp contacts 6 x Ø 2 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Data management status

Article revision	05
------------------	----

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Note	Order information: Order crimp contacts Ø 2 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Contact diameter	Signal contacts
Litz wire cross-section	Signal contacts min.
Litz wire cross-section	Signal contacts max.
Nominal current per signal contact	1 mm ²
Rated voltage Signal contact	2.5 mm ²
Rated surge voltage	20 A
Overvoltage category	48 V AC
Degree of pollution	1.5 kV
Degree of pollution	III
Degree of pollution	3

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	6 mm ... 10 mm
-------------------------	----------------

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Seal material

NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

CA-06S1N8A8007 - Cable connector


1619722

<https://www.phoenixcontact.com/us/products/1619722>



Drawings

Schematic diagram



Connector pin assignment

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619722>

cUL Recognized				
Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	10 A	14 - 14	-

UL Recognized				
Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	17 A	14 - 14	-

cULus Recognized

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-06S1N8A8007 - Cable connector

1619722

<https://www.phoenixcontact.com/us/products/1619722>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1482b071-1e0d-4b8d-86e3-8406f542f578

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com