




THR solder connection pin headers



SL-SMT 5.00/90
SL-SMT 5.08/90



SL-SMT 5.00/90 Box
SL-SMT 5.08/90 Box



Reflow soldering is no longer restricted to SMD's (Surface Mount Devices).

Using a combination of special high temperature resistant plastic and innovative component design, Weidmueller has developed THT (Through-Hole Technology) pin-headers and pcb terminals that can be 100 % incorporated into the automatic pcb assembly process.

These components are supplied as standard in cartons, or anti-static Tape-on-Reel packaging for integration into automatic Pick-&-Place machines.

The high-tech plastic has a melting point greater than 300 °C and so is perfect for the Reflow soldering process or higher temperatures associated with Lead-Free Wave soldering.

The Weidmueller SMT/THR components aid the reduction of overall production costs thus improving manufacturing efficiency.

For additional information about the Weidmueller SMT/THR components, please review our SMT microsite – <http://www.SMT-Technology.com>

- 250 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

Technical data

Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Clamping range, max.	mm ²		
Solid H05(07) V-U	mm ²		
Stranded H07 V-R	mm ²		
Flexible H05(07) V-K	mm ²		
Flexible with ferrule	mm ²		
Ferrule with plastic collar	mm ²		
Stripping length	mm		

Rated current at ambient temperature

	20°C	40°C
A	19.0	16.0

Overvoltage category

	III	III	II
Pollution severity	3	2	2

Rated voltage	V	250	320	400
Rated impulse voltage	kV	4.0	4.0	4.0

UL 1059 rated data - E60693

	B	C	D
Rated voltage	V	300	300
Rated current	A	15.0	10.0
AWG conductor			

CSA C22.2 rated data - LR12400 B

	B	C	D
Rated voltage	V	300	300
Rated current	A	15.0	10.0
AWG conductor			

Material data

Type of insulating material	LCP GF
Flammability class acc. UL94	V-0
Contact base material	CuSn
Contact plating	tin plated

Information

- Gold-plated contact surfaces on request
- Rated current refers to rated cross-section and min. number of poles
- Hole diameter D = 1.4 + 0.1 mm
- Hole diameter D = 1.5 + 0.1 mm for more than 8 poles
- Drawing information P = Pitch

Ordering data

Solder pin length	1.5 mm	3.2 mm
Colour	black	black

Pitch 5.00 mm



Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
2	5.00	(0.197)	100	1796930000	1839890000
3	10.00	(0.394)	100	1796940000	1839900000
4	15.00	(0.591)	100	1796950000	1839910000
5	20.00	(0.787)	50	1796960000	1839920000
6	25.00	(0.984)	50	1796970000	1839930000
7	30.00	(1.181)	50	1796980000	1839940000
8	35.00	(1.378)	50	1796990000	1839950000
9	40.00	(1.575)	50	1797000000	1839960000
10	45.00	(1.772)	50	1797010000	1839970000
11	50.00	(1.969)	50	1797020000	1839980000
12	55.00	(2.165)	50	1797030000	1839990000
13	60.00	(2.362)	50	1797040000	1840000000
14	65.00	(2.559)	50	1797050000	1840010000
15	70.00	(2.756)	50	1797060000	1840020000
16	75.00	(2.953)	50	1797070000	1840030000
17	80.00	(3.150)	20		1840040000
18	85.00	(3.346)	20		1840050000
19	90.00	(3.543)	20		1840060000
20	95.00	(3.740)	20		1840070000
21	100.00	(3.937)	20		1840080000
22	105.00	(4.134)	20		1840090000
23	110.00	(4.331)	20		1840100000
24	115.00	(4.528)	20		1840110000

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
2	5.08	(0.200)	100	1774762001	1779950000
3	10.16	(0.400)	100	1774772001	1779960000
4	15.24	(0.600)	100	1774782001	1779970000
5	20.32	(0.800)	50	1774792001	1779980000
6	25.40	(1.000)	50	1774802001	1779990000
7	30.48	(1.200)	50	1774812001	1780000000
8	35.56	(1.400)	50	1774822001	1780010000
9	40.64	(1.600)	50	1774832001	1780020000
10	45.72	(1.800)	50	1774842001	1780030000
11	50.80	(2.000)	50	1774852001	1780040000
12	55.88	(2.200)	50	1774862001	1780050000
13	60.96	(2.400)	50	1774872001	1780060000
14	66.04	(2.600)	50	1774882001	1780070000
15	71.12	(2.800)	50	1774892001	1780080000
16	76.20	(3.000)	50	1774902001	1780090000
17	81.28	(3.200)	20	1774912001	1780100000
18	86.36	(3.400)	20	1774922001	1780110000
19	91.44	(3.600)	20	1774932001	1780120000
20	96.52	(3.800)	20	1774942001	1780130000
21	101.60	(4.000)	20	1774952001	1780140000
22	106.68	(4.200)	20	1774962001	1780150000
23	111.76	(4.400)	20	1774972001	1780160000
24	116.84	(4.600)	20	1774982001	1780170000

Omnimate Range
Pitch 5.00 / 5.08


Accessories




See page L.10



See page L.24



See page L.11



See page L.16



Pitch 5.00mm: Tape width W = 56mm
Pitch 5.08: Tape width W = 32mm up to 3 poles, otherwise 56mm