

KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Membrane keypad, self-adhesive, copper conduction technology, 4 keys, embossed, 4 colors, connecting cable: 47.3 mm, pitch: 1.0 mm, operating temperature: 0 °C ... 45 °C



Commercial data

Item number	2203574
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFAAD
GTIN	4055626485270
Weight per piece (including packing)	15.2 g
Weight per piece (excluding packing)	15.2 g
Customs tariff number	85365011
Country of origin	HU

KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

Technical data

Product properties

Product type	Membrane keypad
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU
Number of positions	4
Pitch	1 mm
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm
Number of socket pins	6
Number of keys	4

Data management status

Article revision	00
------------------	----

Dimensions

Length	47.3 mm (Membrane cable)
Pitch	1 mm
Dimensions	95 mm x 72 mm

Material specifications

Housing material	Polyester
------------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 45 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

Mounting

Mounting type	Self-adhesive
---------------	---------------

KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

Classifications

ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com