

1419885

<https://www.phoenixcontact.com/us/products/1419885>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, adapter for patch cables, the matching patch cables can be found in the accessories list

Commercial data

Item number	1419885
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	BF7ACE
Catalog page	Page 591 (C-2-2019)
GTIN	4055626253237
Weight per piece (including packing)	12.9 g
Weight per piece (excluding packing)	12.2 g
Customs tariff number	85389099
Country of origin	PL

HC-M-RJ45-AD-PC-M - Contact insert module



1419885

<https://www.phoenixcontact.com/us/products/1419885>

Technical data

Notes

General	Use the patch cable from the accessories list.
General	Connectors may be operated only when there is no load/voltage.

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
	IMPORTANT: Patch cables with a protector over the locking mechanism must be pretreated for use in this module. The protector over the locking mechanism must be extensively removed using a diagonal cutter so that the patch cable can be inserted without a collision with the neighboring module.

Product properties

Product type	Modular contact insert
Series	HC-M-RJ45
Application	Data
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Contact numbering	1 - 8
Number of module slots	1
Type	RJ45

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	34.2 mm
Height	50.7 mm
Length	14.6 mm

Mechanical characteristics

Minimum housing height	72 mm
------------------------	-------

HC-M-RJ45-AD-PC-M - Contact insert module



1419885

<https://www.phoenixcontact.com/us/products/1419885>

Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	0.8 kV
Rated current	1 A
Transmission characteristics (category)	CAT6

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact carrier material	PC
Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

Standards and regulations

Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---

HC-M-RJ45-AD-PC-M - Contact insert module


1419885

<https://www.phoenixcontact.com/us/products/1419885>



Drawings

Dimensional drawing



Male insert

HC-M-RJ45-AD-PC-M - Contact insert module



1419885

<https://www.phoenixcontact.com/us/products/1419885>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419885>

**DNV**
Approval ID: TAE000037S

**CSA**
Approval ID: 13631

**UL Recognized**
Approval ID: E118976

**EAC**
Approval ID: RU C-DE.BL08.B.00511

HC-M-RJ45-AD-PC-M - Contact insert module



1419885

<https://www.phoenixcontact.com/us/products/1419885>

Classifications

ECLASS

ECLASS-11.0	27440218
ECLASS-12.0	27440218
ECLASS-13.0	27440218

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-RJ45-AD-PC-M - Contact insert module



1419885

<https://www.phoenixcontact.com/us/products/1419885>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.071 kg CO2e

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com