



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Approval Sheet For Product Specification

Issued Date: Nov, 14, 2007

Product Name: SAW Filter 2122.5 MHz SMD 3.0X3.0 mm

TST Parts No.: TA0743A

Customer Parts No.: _____

Company: _____
Division: _____
Approved by : _____
Date: _____

Checked by: _____ Bob Chau

Approval by: _____ Francis Chen

Date: _____ 11, 14, 2007



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

SAW Filter 2122.5 MHz

MODEL NO.:TA0743A

REV. NO.:2

A. MAXIMUM RATING:


1. Input Power Level: 10 dBm
2. DC Voltage : 3V
3. Operating Temperature: -20°C to +70°C
4. Storage Temperature: -40°C to +85°C

RoHS Compliant
Lead free
Lead-free soldering


B. ELECTRICAL CHARACTERISTICS:

Item	Unit	Min.	Type.	Max.	Note
Center Frequency Fc	MHz	-	2122.5	-	-
Insertion Loss (2115 ~ 2130 MHz) IL	dB	-	2.1	3	-
Amplitude Ripple (2115 ~ 2130 MHz)	dB	-	0.3	1.3	-
VSWR (2115 ~ 2130 MHz)		-	1.4	2.5	-
Attenuation (Reference level from 0 dB)					
1900 ~ 2050 MHz	dB	33	36	-	-
2180 ~ 2300 MHz	dB	35	45	-	-

C. MEASUREMENT CIRCUIT:




D.OUTLINE DRAWING:





△ : Year Code (2006->6, ..., 2009->9)

□ : Date Code (Follow the table from planner each year)

E. PCB Footprint:





F. Frequency Characteristics :





Reflection Functions :

S11



S22



H. RECOMMENDED REFLOW PROFILE :

