


ELV/XP SERIES PART NUMBERING SCHEME

REV	ECN	APPD
-	3624	JEC 1/18/99
A	3865	JEC 11/9/99
B	4661	IQ 11/26/01
C	5742	2/12/28/05



RATINGS

CURRENT - 12A
VOLTAGE - 300V
U.L. FILE NO. E83421



RATINGS

CURRENT - 12A
VOLTAGE - 300V
CSA FILE NO. LR69703

CONSULT PCD FOR PART NO. AND
AVAILABILITY OF FOLLOWING OPTIONS:

- * CUSTOM COLORS
- * CUSTOM MARKING
- * CUSTOM KEYING
- * SELECTIVE CONTACT LOADING

DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT - 12A
VOLTAGE - 300 V
TUV FILE NO. 20396

**INSTALLATION
RECOMMENDATIONS:**
WIRE RANGE: AWG #16-28, STRANDED
OR SOLID
WIRE STRIP LENGTH: .250"
TIGHTENING TORQUE: 2.2 LB-IN.

MATERIALS:
HOUSING: PA 4/6, UL 94 V-0
CONTACT: COPPER ALLOY, OPTIONAL FINISH
SCREW: COPPER ALLOY, NICKEL FINISH
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH

MAX OPERATING TEMPERATURE:
125°C


DIMENSIONS

ANSI Y14.5M
UNITS: INCHES
ACAD FILE

TOLERANCES

.XX ±.01
.XXX ±.005
ANGLES ±2°

PROJECTION



Amphenol Pcd SPECIFICATION DRAWING

ENGR
I. QUINN 12/21/99

CHKD
J. CAHALY 1/18/99

APPD
J. CAHALY 1/18/99

TITLE

ELV/ELX SERIES
PLUGGABLE TERMINAL
BLOCK, RIGHT ANGLE

ORIGINAL
STAMPED
IN RED


THIS DOCUMENT CONTAINS
PROPRIETARY INFORMATION WHICH
IS THE CONFIDENTIAL PROPERTY
OF AMPHENOL PCD INC. PEABODY, MA

SIZE
A


DWG NO.
ELVP02100

REV
C



CODE: 58982 SCALE: NONE SHEET 1 OF 2





STANDARD R/A PLUG



L=NUM OF POS X CL SPACING



MOUNTING EAR CONFIGURATION



SIZE	DWG NO.	DOC REV
A	ELVP02100	C
CODE: 58982	SCALE: NONE	SHEET 2 OF 2