

1107999

https://www.phoenixcontact.com/us/products/1107999

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M12-Push-pull external locking, Front mounting, SMD

Your advantages

- · Manufacturer-independent M12 push-pull locking system for maximum availability
- · Easy and quick cabling of devices and systems in hard-to-reach areas
- · Easy device integration, thanks to mechanical port screw connections with threaded fastening
- · Flexible PCB assembly: two-piece connectors for wave and THR soldering

Commercial data

Item number	1107999
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQBAB
GTIN	4063151011475
Weight per piece (including packing)	8.77 g
Weight per piece (excluding packing)	8.77 g
Customs tariff number	79070000
Country of origin	DE



1107999

https://www.phoenixcontact.com/us/products/1107999

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

Product properties

Product type	Panel mounting base	
Thread type	M12	
Data management status		

Connection data

Connection method	SMD
Connection method	SIVID

Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Material of grip body	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Pin
Head thread type	M12
Head locking type	Push-pull external locking

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)

Standards and regulations

M12

Standard designation	M12 connector



1107999

https://www.phoenixcontact.com/us/products/1107999

	Standards/specifications	IEC 61076-2-010
	Note	Push-pull
Mounting		
	Mounting type	Front mounting



1107999

https://www.phoenixcontact.com/us/products/1107999

Classifications

ECLASS

	<i>5</i> 27.000			
	ECLASS-11.0	27440224		
	ECLASS-12.0	27440224		
	ECLASS-13.0	27440224		
ΕΊ	ETIM			
	ETIM 9.0	EC003556		
UNSPSC				
	UNSPSC 21.0	39121400		



1107999

https://www.phoenixcontact.com/us/products/1107999

Environmental product compliance

EU RoHS

20 1.01.0	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com