



| NO. | MASSE / DIMENSION |
|-----|-------------------|
| A   | 31.8              |
| B   | 1-20UNEF-2B       |
| C   | 7/8-20UNEF-2A     |
| D   | 57                |
| E   | 15.2              |
| F   | 25                |
| G   | 9.4               |

| NO. | BESCHREIBUNG / DESCRIPTION              |
|-----|-----------------------------------------|
| 2   | ISOLIERKÖRPER BUCHSE / INSULATOR SOCKET |
| 3   | DICHTKÖRPER / GROMMET                   |
| 4   | ENDRING / ENDRING                       |
| 6   | KONTAKTBUCHSE / CONTACT SOCKET          |
| 7   | ZYLINDERGHÄUSE / BARREL                 |
| 9   | ÜBERWURFMUTTER / COUPLING NUT           |
| 14  | F-ENDGEHÄUSE / F-ENDBELL                |

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| Note: Due to an automatic nomenclature system, numbers generated may not be sequential.            |
| Specification and Dimensions subject to change<br>Drawings illustrate normal insulator positioning |

|                                                                 |
|-----------------------------------------------------------------|
| Material Specification:                                         |
| Shell Material: Aluminium alloy                                 |
| Shell Plating: Olive drab chromate coating over cadmium plating |
| Insulator Material: Neoprene                                    |
| Contact Material: Copper alloy                                  |
| Contact Plating: Hard silver                                    |

|                                                                                                                                                                                                     |                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| all dimensions are in mm<br>Dimensions without tolerance indications are general tolerances in acc. with DIN7168m                                                                                   | drawing for<br>CUSTOMER                                                                                                                    |
| <br><b>ITT</b><br><i>Engineered for life</i><br><small>ITT CANNON GmbH<br/>D - 71384 Weinstadt/Germany</small> | description<br><b>CA3108F16-10S-F80-F0</b><br><b>Plug 90°</b><br><b>Endbell for flex tube</b><br><b>AWG Crimp / Socket / Layout: 16-10</b> |
| <small>© All rights reserved. Reproduction or issue to third in any form<br/>whatever is only permitted with written authorization of ITT Cannon</small>                                            | page<br>1/1<br>revision<br>1765 29. Aug 24                                                                                                 |