

OKR-T/10-W12-C

In Production

Recommended

RoHS

Appearance & Shape



Features

10A, 12V Input Non-Isolated DC-DC Converter, 4.5-14Vin, 0.591 to 6.0Vout, Positive on/off control, SIP

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

OKR-T/10-W12-C



Specifications

Iout(A)Max	10A
Vin(V)	4.5V to 14V
Vin(V)typ	12V
Vout(V)	0.591V to 6V
LineRegulation (%)	-0.3% to 0.3%
LoadRegulation (%)	-0.75% to 0.75%
Outputs (#)	1
Efficiency (%)	92%
Size(mm)W	16.5mm
Size(mm)L	10.4mm
Size(mm)T	7.62mm
Operatingtemperature(degC)	-40°C to 85°C
Package	SIP
Type	Modules (integrated components)
Productseries	OKR
Product Series Features	Adjustable Output 10-Amp SIP-mount DC-DC Converters
Brand	Murata Power Solutions

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.