



## Ultra-Fast Recovery Diodes

Reverse Voltage-400V

Forward current-16A

### Features

Ultra-Fast Recovery chip

Fast reverse recovery time

Ideal for surface mounted applications

Low power loss, high efficiency

Plastic Case Material has UL Flammability

### Mechanical Data

Package: TO-220F


Terminals: Tin Plated leads, solderable per

Mil-STD-750 Method 2026

Polarity: As marked

Molding compound meets UL 94 V-0 flammability rating,

ROHS-compliant



TO-220F

### Maximum Ratings (Ta=25°C Unless otherwise specified)

Type Number	SYMBOL	MURF1640CT	Unit
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	400	V
Maximum RMS Voltage	$V_{RMS}$	280	V
Maximum DC Blocking Voltage	$V_{DC}$	400	V
Maximum Average Forward Rectified Current	$I_{O(AV)}$	16.0	A
Peak Forward Surge Current 8.3ms Single half-sine-wave superimposed on rated load(JEDEC Method) on rated	IFSM	180.0	A
Maximum Forward Voltage at 16 A DC	$V_{FM}$	1.35	V
Maximum Reverse Current TA = 25°C	IR	5	uA
at Rated DC Blocking Voltage TA = 100°C		200	
Reverse Recovery Time	Trr	35	ns
Typical Thermal Resistance Between junction and ambient Between Junction and Case	$R_{QJa}$	50.0	°C/W
	$R_{QJc}$	4.0	
Operating Junction Temperature Range	$T_J$	—55to+150	°C
Storage Temperature Range	$T_{STG}$	—55to+150	°C



FIG. 1 MAXIMUM AVERAGE FORWARD CURRENT DERATING




FIG. 2 TYPICAL FORWARD CHARACTERISTICS




FIG. 3 MAXIMUM NON-REPEITIVE SURGE CURRENT






FIG. 4 TYPICAL REVERSE CHARACTERISTICS(per element)






## MARKING INFORMATION

TO-220F/FAC



—⏏— = Polar line

 = Logo

\*\*\*\*\* = Date Code Marking

MURF\*\*\*\*\* = Marking Code

Date Code Marking

<u>A</u>	<u>001</u>
Year/month code	Order serial number

Example: January 2023 order number is 001, period A001

January 2025 Order number is 001, period <sup>•</sup>A001

Period code year distinction					
2023/2024	2025/2026	2027/2028	2029/2030	2031/2032	remark
no	first	second	tertius	fourth	Dot above corresponding character

eriod code month code mapping table												
month	1	2	3	4	5	6	7	8	9	10	11	12
Single year (Example 2023)	A	B	C	D	E	F	G	H	I	J	K	L
Biennial (example 2024)	M	N	O	P	Q	R	S	T	U	V	W	X



### Package Outline Dimensions millimeters

TO-220F/AC					
DIM	INCHES		MM		NOTE
	min	max	min	max	
A	—	0.41	—	10.30	
B	0.61	0.64	15.60	16.20	
C	0.18	0.19	4.50	4.90	
D	0.26	0.28	6.60	7.00	
E	0.50	0.53	12.80	13.40	
a	0.10	0.10	2.45	2.65	
b	—	0.16	—	4.10	
c	0.03	0.04	0.72	0.92	
d	0.02	0.02	0.40	0.60	
e	—	0.15	—	3.80	Ø
f	0.09	0.11	2.40	2.80	

### Important Statements and disclaimers.

Do not copy or modify file information without permission.

Xumao Micro reserves the right to modify this document and its products.

Specifications are available without prior notice. Customer shall obtain and confirm the latest product information and specifications prior to final design, purchase or use.

Xumao Micro does not assume any implied warranties, including warranties of fitness for special purposes, non-infringement and merchantability.

The products shown here are not designed and licensed for demanding equipment at a level of reliability or for human life and any life-saving related applications or life-sustaining, such as medical devices, transportation equipment, aerospace machinery, and so on. Customers who use or sell these products for such applications do so at their own risk.

As Xumao Micro uses batch number as tracking benchmark, please provide batch number for tracking in case of exception.